

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302124

Luminaire Tested: P3AS17R60W2N902750DE010 E3DLP1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302124  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R60W2N902750DE010 E3DLP1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,  
E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 787.0 lumens  
Efficiency: N/A  
Efficacy: 40.6 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302124  
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1WMH\_2700K

### Luminous Intensity Polar Plot







TEST NUMBER: P1302124

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.5	10.5
10°-20°	200.4	25.5
20°-30°	219.8	27.9
30°-40°	160.1	20.3
40°-50°	75.6	9.6
50°-60°	24.8	3.1
60°-70°	14.0	1.8
70°-80°	7.6	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	502.6	63.9
0°-40°	662.7	84.2
0°-60°	763.1	97.0
0°-90°	787.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	910	
5°	886	82
15°	721	200
25°	481	220
35°	255	160
45°	95	76
55°	25	25
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1302124  
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	909.6
2.5°	904.2
5°	885.8
7.5°	857.7
10°	819.8
12.5°	774.4
15°	721.4
17.5°	664.1
20°	603.5
22.5°	541.8
25°	481.3
27.5°	420.7
30°	363.4
32.5°	308.2
35°	255.2
37.5°	207.7
40°	164.4
42.5°	126.5
45°	95.2
47.5°	69.2
50°	47.6
52.5°	31.4
55°	24.9
57.5°	21.6
60°	19.5
62.5°	16.2
65°	14.1
67.5°	11.9
70°	9.7
72.5°	8.7
75°	7.6
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)