

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300121

Luminaire Tested: P3AS17R30W2N902750DE010 E3CD1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R30W2N902750DE010 E3CD1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,
E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1534.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300121
CATALOG NUMBER: P3AS17R30W2N902750DE010 E3CD1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1300121

CATALOG NUMBER: P3AS17R30W2N902750DE010 E3CD1MW_500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	511.8	33.4
10°-20°	797.7	52.0
20°-30°	185.2	12.1
30°-40°	28.7	1.9
40°-50°	4.9	0.3
50°-60°	2.3	0.1
60°-70°	1.9	0.1
70°-80°	1.3	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1494.7	97.4
0°-40°	1523.4	99.3
0°-60°	1530.6	99.8
0°-90°	1534.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1534.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5697	
5°	5568	512
15°	3028	798
25°	319	185
35°	35	29
45°	5	5
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1300121
CATALOG NUMBER: P3AS17R30W2N902750DE010 E3CD1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5696.8
1°	5693.2
2°	5677.5
3°	5651.0
4°	5617.3
5°	5567.9
6°	5506.4
7°	5414.8
8°	5289.5
9°	5105.2
10°	4872.6
11°	4572.6
12°	4234.0
13°	3858.1
14°	3444.8
15°	3027.9
17.5°	1980.9
20°	1118.1
22.5°	571.1
25°	319.3
27.5°	196.4
30°	120.5
32.5°	65.1
35°	34.9
37.5°	22.9
40°	14.5
42.5°	8.4
45°	4.8
47.5°	3.6
50°	3.6
52.5°	2.4
55°	2.4
57.5°	2.4
60°	2.4
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1300121
CATALOG NUMBER: P3AS17R30W2N902750DE010 E3CD1MW_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)