

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300131

Luminaire Tested: P3AS17R30W2N902750DE010 E3D1LI\_5000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300131  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R30W2N902750DE010 E3D1LI\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,  
E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1521.0 lumens  
Efficiency: N/A  
Efficacy: 78.4 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300131  
CATALOG NUMBER: P3AS17R30W2N902750DE010 E3D1LI\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1300131

CATALOG NUMBER: P3AS17R30W2N902750DE010 E3D1LI\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	496.1	32.6
10°-20°	769.3	50.6
20°-30°	198.4	13.0
30°-40°	46.6	3.1
40°-50°	9.1	0.6
50°-60°	1.1	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1463.8	96.2
0°-40°	1510.4	99.3
0°-60°	1520.5	100.0
0°-90°	1521.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1521.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5519	
5°	5426	496
15°	2920	769
25°	362	198
35°	69	47
45°	11	9
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1300131

CATALOG NUMBER: P3AS17R30W2N902750DE010 E3D1LI\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5518.7
1°	5514.6
2°	5501.6
3°	5486.9
4°	5465.0
5°	5426.0
6°	5362.9
7°	5257.8
8°	5114.3
9°	4927.1
10°	4683.3
11°	4393.4
12°	4076.9
13°	3712.6
14°	3331.2
15°	2919.7
16°	2516.4
17°	2127.9
18°	1755.3
19°	1413.5
20°	1125.4
21°	885.6
22°	696.7
23°	551.5
24°	441.6
25°	362.5
26°	302.3
27°	256.8
28°	222.0
29°	190.1
30°	161.2
32.5°	101.6
35°	69.1
37.5°	43.1
40°	24.8
42.5°	16.5
45°	11.2
47.5°	6.5
50°	3.0
52.5°	1.2
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P1300131  
CATALOG NUMBER: P3AS17R30W2N902750DE010 E3D1LI\_5000K

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)