

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302219

Luminaire Tested: P3AS17R60W2N902765DE010 E3DL1WH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302219  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R60W2N902765DE010 E3DL1WH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 787.0 lumens  
Efficiency: N/A  
Efficacy: 40.6 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302219  
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1WH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1302219

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1WH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	199458
5°	194981
10°	182539
15°	163769
20°	140829
25°	116450
30°	92014
35°	68315
40°	47060
45°	29522
50°	16238
55°	9519
60°	8552
65°	7316
70°	6219
75°	6439
80°	5430
85°	5535

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29522 cd/sqm



TEST NUMBER: P1302219

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1WH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	82.5	10.5
10°-20°	200.4	25.5
20°-30°	219.8	27.9
30°-40°	160.1	20.3
40°-50°	75.6	9.6
50°-60°	24.8	3.1
60°-70°	14.0	1.8
70°-80°	7.6	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	502.6	63.9
0°-40°	662.7	84.2
0°-60°	763.1	97.0
0°-90°	787.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	910	
5°	886	82
15°	721	200
25°	481	220
35°	255	160
45°	95	76
55°	25	25
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1302219

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1WH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	909.6
2.5°	904.2
5°	885.8
7.5°	857.7
10°	819.8
12.5°	774.4
15°	721.4
17.5°	664.1
20°	603.5
22.5°	541.8
25°	481.3
27.5°	420.7
30°	363.4
32.5°	308.2
35°	255.2
37.5°	207.7
40°	164.4
42.5°	126.5
45°	95.2
47.5°	69.2
50°	47.6
52.5°	31.4
55°	24.9
57.5°	21.6
60°	19.5
62.5°	16.2
65°	14.1
67.5°	11.9
70°	9.7
72.5°	8.7
75°	7.6
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)