

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302311

Luminaire Tested: P3AS17R65W2N902750DE010 E3CB1MMS\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1302311  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R65W2N902750DE010 E3CB1MMS\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 90CRI ,  
E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1499.0 lumens  
Efficiency: N/A  
Efficacy: 77.3 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302311  
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MMS\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1302311  
 CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MMS\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75	75	75	75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51	51	51	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	366330
5°	344771
10°	340386
15°	334395
20°	315704
25°	293025
30°	227757
35°	131758
40°	53099
45°	24437
50°	9518
55°	3708
60°	3201
65°	3165
70°	3077
75°	3050
80°	3031
85°	3019

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24437 cd/sqm



TEST NUMBER: P1302311

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MMS\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.9	9.9
10°-20°	411.3	27.4
20°-30°	538.4	35.9
30°-40°	311.9	20.8
40°-50°	66.7	4.5
50°-60°	10.9	0.7
60°-70°	6.0	0.4
70°-80°	3.5	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1098.7	73.3
0°-40°	1410.5	94.1
0°-60°	1488.2	99.3
0°-90°	1499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1499.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1671	
5°	1566	149
15°	1473	411
25°	1211	538
35°	492	312
45°	79	67
55°	10	11
65°	6	6
75°	4	3
85°	1	1
90°	0	



TEST NUMBER: P1302311  
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3CB1MMS\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1670.6
2.5°	1623.3
5°	1566.3
7.5°	1543.3
10°	1528.7
12.5°	1508.1
15°	1473.0
17.5°	1418.4
20°	1352.9
22.5°	1291.1
25°	1211.1
27.5°	1076.5
30°	899.5
32.5°	697.1
35°	492.2
37.5°	311.6
40°	185.5
42.5°	116.4
45°	78.8
47.5°	50.9
50°	27.9
52.5°	13.3
55°	9.7
57.5°	8.5
60°	7.3
62.5°	7.3
65°	6.1
67.5°	4.8
70°	4.8
72.5°	3.6
75°	3.6
77.5°	2.4
80°	2.4
82.5°	1.2
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)