

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302352

Luminaire Tested: P3AS17R65W2N902750DE010 E3D1WH\_5000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R65W2N902750DE010 E3D1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,  
E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1438.1 lumens  
Efficiency: N/A  
Efficacy: 74.1 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302352  
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3D1WH\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1302352

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3D1WH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.3	10.7
10°-20°	409.3	28.5
20°-30°	518.0	36.0
30°-40°	295.0	20.5
40°-50°	58.6	4.1
50°-60°	3.1	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1080.5	75.1
0°-40°	1375.5	95.6
0°-60°	1437.2	99.9
0°-90°	1438.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1438.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1757	
5°	1625	153
15°	1469	409
25°	1161	518
35°	470	295
45°	69	59
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1302352  
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3D1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1757.2
1°	1744.2
2°	1715.8
3°	1682.7
4°	1650.2
5°	1625.4
6°	1607.1
7°	1592.3
8°	1579.3
9°	1566.3
10°	1553.9
11°	1540.3
12°	1526.1
13°	1509.0
14°	1490.6
15°	1468.8
16°	1442.8
17°	1414.4
18°	1383.7
19°	1351.2
20°	1321.0
21°	1290.3
22°	1262.5
23°	1233.5
24°	1199.8
25°	1160.8
26°	1114.1
27°	1058.0
28°	994.7
29°	927.4
30°	857.0
31°	779.6
32°	702.8
32.5°	663.2
33°	624.7
34°	546.7
35°	469.9
36°	399.0
37°	328.6
37.5°	292.6
38°	263.6
39°	213.4
40°	174.4
42.5°	107.6
45°	68.6



TEST NUMBER: P1302352  
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3D1WH\_5000K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	40.2
50°	14.8
52.5°	3.0
55°	1.8
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)