

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300265

Luminaire Tested: P3AS17R30W2N902765DE010 E3CB1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R30W2N902765DE010 E3CB1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1520.0 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300265
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3CB1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1300265

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3CB1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	91	90	89
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	87	86
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	85	84	83
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83	82	81
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76	75	74
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1237796
5°	1214393
10°	1075064
15°	681116
20°	258532
25°	76553
30°	30232
35°	9262
40°	4093
45°	1489
50°	1228
55°	918
60°	1053
65°	1245
70°	769
75°	1017
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 80°
 Luminance: 1515 cd/sqm



TEST NUMBER: P1300265

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3CB1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	507.2	33.4
10°-20°	790.4	52.0
20°-30°	183.5	12.1
30°-40°	28.4	1.9
40°-50°	4.9	0.3
50°-60°	2.3	0.2
60°-70°	1.9	0.1
70°-80°	1.3	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1481.1	97.4
0°-40°	1509.5	99.3
0°-60°	1516.7	99.8
0°-90°	1520.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1520.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5645	
5°	5517	507
15°	3000	790
25°	316	184
35°	35	28
45°	5	5
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1300265
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3CB1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5644.8
1°	5641.2
2°	5625.7
3°	5599.4
4°	5566.0
5°	5517.0
6°	5456.1
7°	5365.4
8°	5241.2
9°	5058.6
10°	4828.2
11°	4530.9
12°	4195.4
13°	3822.9
14°	3413.4
15°	3000.3
17.5°	1962.8
20°	1107.9
22.5°	565.9
25°	316.4
27.5°	194.6
30°	119.4
32.5°	64.5
35°	34.6
37.5°	22.7
40°	14.3
42.5°	8.4
45°	4.8
47.5°	3.6
50°	3.6
52.5°	2.4
55°	2.4
57.5°	2.4
60°	2.4
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1300265
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3CB1MW_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)