

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300291

Luminaire Tested: P3AS17R30W2N902765DE010 E3D1H\_4000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1300291  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R30W2N902765DE010 E3D1H\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1530.0 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300291

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3D1H\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1300291

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3D1H\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 97  | 97  | 97  |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99  | 100 | 98  | 97  | 97  | 96  | 95  | 94  | 94  | 94  | 94  |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 97  | 95  | 97  | 95  | 93  | 95  | 93  | 92  | 90  | 90  | 90  | 90  |
| 4   | 105 | 99  | 95  | 92  | 103 | 98  | 95  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 93  | 91  | 89  | 88  | 88  | 88  | 88  |
| 5   | 101 | 96  | 92  | 89  | 100 | 95  | 91  | 88  | 93  | 90  | 87  | 92  | 89  | 87  | 90  | 88  | 86  | 85  | 85  | 85  | 85  |
| 6   | 99  | 92  | 88  | 85  | 97  | 92  | 88  | 85  | 90  | 87  | 85  | 89  | 86  | 84  | 88  | 85  | 83  | 82  | 82  | 82  | 82  |
| 7   | 96  | 89  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  | 87  | 84  | 81  | 86  | 83  | 81  | 80  | 80  | 80  | 80  |
| 8   | 93  | 87  | 83  | 80  | 92  | 86  | 82  | 80  | 85  | 82  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 78  | 78  | 78  | 78  |
| 9   | 91  | 84  | 80  | 77  | 90  | 84  | 80  | 77  | 83  | 79  | 77  | 82  | 79  | 77  | 82  | 79  | 77  | 76  | 76  | 76  | 76  |
| 10  | 88  | 82  | 78  | 75  | 88  | 81  | 78  | 75  | 81  | 77  | 75  | 80  | 77  | 75  | 80  | 77  | 75  | 74  | 74  | 74  | 74  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1217315 |
| 5°  | 1201450 |
| 10° | 1048967 |
| 15° | 666746  |
| 20° | 264156  |
| 25° | 88239   |
| 30° | 41044   |
| 35° | 18605   |
| 40° | 7128    |
| 45° | 3504    |
| 50° | 1023    |
| 55° | 459     |
| 60° | 263     |
| 65° | 311     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3504 cd/sqm



TEST NUMBER: P1300291

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3D1H\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 499.0  | 32.6      |
| 10°-20°   | 773.9  | 50.6      |
| 20°-30°   | 199.5  | 13.0      |
| 30°-40°   | 46.9   | 3.1       |
| 40°-50°   | 9.1    | 0.6       |
| 50°-60°   | 1.1    | 0.1       |
| 60°-70°   | 0.5    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1472.4 | 96.2      |
| 0°-40°    | 1519.3 | 99.3      |
| 0°-60°    | 1529.5 | 100.0     |
| 0°-90°    | 1530.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1530.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5551 |      |
| 5°  | 5458 | 499  |
| 15° | 2937 | 774  |
| 25° | 365  | 200  |
| 35° | 70   | 47   |
| 45° | 11   | 9    |
| 55° | 1    | 1    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1300291

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3D1H\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5551.4 |
| 1°    | 5547.2 |
| 2°    | 5534.2 |
| 3°    | 5519.3 |
| 4°    | 5497.4 |
| 5°    | 5458.2 |
| 6°    | 5394.6 |
| 7°    | 5288.9 |
| 8°    | 5144.6 |
| 9°    | 4956.3 |
| 10°   | 4711.0 |
| 11°   | 4419.4 |
| 12°   | 4101.0 |
| 13°   | 3734.6 |
| 14°   | 3350.9 |
| 15°   | 2937.0 |
| 16°   | 2531.3 |
| 17°   | 2140.5 |
| 18°   | 1765.7 |
| 19°   | 1421.9 |
| 20°   | 1132.0 |
| 21°   | 890.9  |
| 22°   | 700.8  |
| 23°   | 554.7  |
| 24°   | 444.3  |
| 25°   | 364.7  |
| 26°   | 304.1  |
| 27°   | 258.4  |
| 28°   | 223.3  |
| 29°   | 191.2  |
| 30°   | 162.1  |
| 32.5° | 102.2  |
| 35°   | 69.5   |
| 37.5° | 43.4   |
| 40°   | 24.9   |
| 42.5° | 16.6   |
| 45°   | 11.3   |
| 47.5° | 6.5    |
| 50°   | 3.0    |
| 52.5° | 1.2    |
| 55°   | 1.2    |
| 57.5° | 0.6    |
| 60°   | 0.6    |
| 62.5° | 0.6    |
| 65°   | 0.6    |



TEST NUMBER: P1300291

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3D1H\_4000K

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 0.6 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)