

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300318

Luminaire Tested: P3AS17R30W2N902765DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R30W2N902765DE010 E3DL1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 562.0 lumens
Efficiency: N/A
Efficacy: 29.0 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300318
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1300318

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	92	92	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	87	87	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	83	83	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	79	79	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	76	76	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	73	73	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	70	70	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	67	67	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	65	65	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	327934
5°	312128
10°	262542
15°	189331
20°	117447
25°	66802
30°	37094
35°	20184
40°	10649
45°	5768
50°	3070
55°	2026
60°	1842
65°	1920
70°	1731
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5768 cd/sqm



TEST NUMBER: P1300318

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	22.7
10°-20°	227.0	40.4
20°-30°	131.2	23.3
30°-40°	49.8	8.9
40°-50°	15.3	2.7
50°-60°	5.1	0.9
60°-70°	3.5	0.6
70°-80°	1.9	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	485.8	86.4
0°-40°	535.6	95.3
0°-60°	556.0	98.9
0°-90°	562.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	562.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1496	
5°	1418	128
15°	834	227
25°	276	131
35°	75	50
45°	19	15
55°	5	5
65°	4	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1300318
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1495.5
1°	1494.5
2°	1485.5
3°	1468.5
4°	1447.2
5°	1418.0
6°	1380.9
7°	1339.5
8°	1293.3
9°	1238.1
10°	1179.1
11°	1115.4
12°	1048.0
13°	977.4
14°	905.7
15°	834.0
17.5°	657.8
20°	503.3
22.5°	373.2
25°	276.1
27.5°	200.7
30°	146.5
32.5°	105.6
35°	75.4
37.5°	52.6
40°	37.2
42.5°	26.0
45°	18.6
47.5°	12.7
50°	9.0
52.5°	6.4
55°	5.3
57.5°	4.8
60°	4.2
62.5°	3.7
65°	3.7
67.5°	3.2
70°	2.7
72.5°	2.1
75°	1.6
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.0



TEST NUMBER: P1300318
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)