

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302605

Luminaire Tested: P3AS17R65W2N902765DE010 E3DLP1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902765DE010 E3DLP1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 828.0 lumens
Efficiency: N/A
Efficacy: 42.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302605
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302605
 CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210466
5°	205216
10°	191112
15°	171284
20°	147923
25°	123031
30°	97028
35°	71902
40°	49550
45°	30732
50°	16682
55°	10513
60°	8903
65°	8042
70°	6860
75°	6100
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30732 cd/sqm



TEST NUMBER: P1302605

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.6	10.5
10°-20°	209.7	25.3
20°-30°	231.9	28.0
30°-40°	168.4	20.3
40°-50°	78.9	9.5
50°-60°	26.6	3.2
60°-70°	15.3	1.9
70°-80°	8.1	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	528.2	63.8
0°-40°	696.6	84.1
0°-60°	802.0	96.9
0°-90°	828.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	960	
5°	932	87
15°	754	210
25°	508	232
35°	269	168
45°	99	79
55°	28	27
65°	16	15
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1302605
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	959.8
2.5°	953.8
5°	932.3
7.5°	900.1
10°	858.3
12.5°	809.4
15°	754.5
17.5°	694.8
20°	633.9
22.5°	570.6
25°	508.5
27.5°	445.3
30°	383.2
32.5°	323.5
35°	268.6
37.5°	218.5
40°	173.1
42.5°	132.5
45°	99.1
47.5°	71.6
50°	48.9
52.5°	33.4
55°	27.5
57.5°	23.9
60°	20.3
62.5°	17.9
65°	15.5
67.5°	13.1
70°	10.7
72.5°	9.6
75°	7.2
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)