

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300365

Luminaire Tested: P3AS17R30W2N902765DE010 E3DLD1H\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300365  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R30W2N902765DE010 E3DLD1H\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 6500K CCT AND, 90CRI ,  
E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 982.0 lumens  
Efficiency: N/A  
Efficacy: 50.6 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300365  
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DLD1H\_6500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1300365

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DLD1H\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.6	9.7
10°-20°	229.8	23.4
20°-30°	259.0	26.4
30°-40°	206.8	21.1
40°-50°	106.3	10.8
50°-60°	40.0	4.1
60°-70°	26.2	2.7
70°-80°	14.1	1.4
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.4	59.5
0°-40°	791.3	80.6
0°-60°	937.5	95.5
0°-90°	982.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	982.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1058	
5°	1030	96
15°	827	230
25°	565	259
35°	333	207
45°	135	106
55°	41	40
65°	26	26
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P1300365  
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DLD1H\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1058.0
1°	1058.0
2°	1054.4
3°	1048.4
4°	1039.9
5°	1030.3
6°	1018.2
7°	1002.6
8°	985.7
9°	966.4
10°	947.1
11°	925.4
12°	902.6
13°	878.5
14°	853.1
15°	826.6
17.5°	759.2
20°	691.7
22.5°	626.6
25°	565.2
27.5°	504.9
30°	448.3
32.5°	390.4
35°	332.6
37.5°	275.9
40°	222.9
42.5°	175.9
45°	135.0
47.5°	100.0
50°	69.9
52.5°	49.4
55°	41.0
57.5°	37.4
60°	33.7
62.5°	30.1
65°	26.5
67.5°	22.9
70°	19.3
72.5°	15.7
75°	13.3
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2



TEST NUMBER: P1300365  
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DLD1H\_6500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)