

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302617

Luminaire Tested: P3AS17R65W2N902765DE010 E3DLP1WMH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302617  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R65W2N902765DE010 E3DLP1WMH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,  
E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 828.0 lumens  
Efficiency: N/A  
Efficacy: 42.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302617  
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1WMH\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1302617

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1WMH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	86.6	10.5
10°-20°	209.7	25.3
20°-30°	231.9	28.0
30°-40°	168.4	20.3
40°-50°	78.9	9.5
50°-60°	26.6	3.2
60°-70°	15.3	1.9
70°-80°	8.1	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	528.2	63.8
0°-40°	696.6	84.1
0°-60°	802.0	96.9
0°-90°	828.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	828.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	960	
5°	932	87
15°	754	210
25°	508	232
35°	269	168
45°	99	79
55°	28	27
65°	16	15
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1302617

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	959.8
2.5°	953.8
5°	932.3
7.5°	900.1
10°	858.3
12.5°	809.4
15°	754.5
17.5°	694.8
20°	633.9
22.5°	570.6
25°	508.5
27.5°	445.3
30°	383.2
32.5°	323.5
35°	268.6
37.5°	218.5
40°	173.1
42.5°	132.5
45°	99.1
47.5°	71.6
50°	48.9
52.5°	33.4
55°	27.5
57.5°	23.9
60°	20.3
62.5°	17.9
65°	15.5
67.5°	13.1
70°	10.7
72.5°	9.6
75°	7.2
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)