

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302630

Luminaire Tested: P3AS17R70W2N902750DE010 E3CB1MMS_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302630
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902750DE010 E3CB1MMS_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1516.0 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302630
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CB1MMS_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302630

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CB1MMS_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	8.1
10°-20°	329.2	21.7
20°-30°	460.0	30.3
30°-40°	426.5	28.1
40°-50°	152.9	10.1
50°-60°	13.0	0.9
60°-70°	6.5	0.4
70°-80°	4.1	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	911.4	60.1
0°-40°	1337.9	88.3
0°-60°	1503.8	99.2
0°-90°	1516.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1516.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1373	
5°	1305	122
15°	1172	329
25°	1002	460
35°	708	426
45°	183	153
55°	10	13
65°	6	6
75°	4	4
85°	1	2
90°	0	



TEST NUMBER: P1302630
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CB1MMS_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1372.8
2.5°	1352.2
5°	1305.0
7.5°	1261.4
10°	1227.4
12.5°	1199.6
15°	1171.7
17.5°	1137.8
20°	1097.8
22.5°	1051.7
25°	1002.1
27.5°	951.2
30°	890.6
32.5°	813.0
35°	707.6
37.5°	573.1
40°	426.5
42.5°	290.8
45°	183.0
47.5°	101.8
50°	43.6
52.5°	14.5
55°	9.7
57.5°	8.5
60°	8.5
62.5°	7.3
65°	6.1
67.5°	6.1
70°	4.8
72.5°	4.8
75°	3.6
77.5°	3.6
80°	2.4
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)