

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302643

Luminaire Tested: P3AS17R70W2N902750DE010 E3CD1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302643
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902750DE010 E3CD1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1494.1 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302643
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CD1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302643

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CD1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 94 | 93 | | | | 93 |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 93 | 97 | 94 | 91 | 94 | 91 | 89 | 91 | 89 | 87 | 85 | | | | 85 |
| 3 | 101 | 94 | 89 | 85 | 99 | 93 | 88 | 84 | 90 | 86 | 83 | 88 | 84 | 81 | 85 | 82 | 80 | 78 | | | | 78 |
| 4 | 95 | 87 | 81 | 77 | 94 | 86 | 81 | 76 | 84 | 79 | 75 | 82 | 78 | 75 | 80 | 77 | 74 | 72 | | | | 72 |
| 5 | 90 | 81 | 75 | 70 | 88 | 80 | 74 | 70 | 78 | 73 | 69 | 77 | 72 | 69 | 75 | 71 | 68 | 66 | | | | 66 |
| 6 | 85 | 75 | 69 | 64 | 83 | 75 | 69 | 64 | 73 | 68 | 64 | 72 | 67 | 63 | 70 | 66 | 63 | 61 | | | | 61 |
| 7 | 80 | 70 | 64 | 59 | 79 | 70 | 64 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 58 | 57 | | | | 57 |
| 8 | 76 | 66 | 59 | 55 | 75 | 65 | 59 | 55 | 64 | 58 | 55 | 63 | 58 | 54 | 62 | 57 | 54 | 53 | | | | 53 |
| 9 | 72 | 62 | 55 | 51 | 71 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 50 | 58 | 54 | 50 | 49 | | | | 49 |
| 10 | 68 | 58 | 52 | 47 | 67 | 57 | 51 | 47 | 56 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 46 | | | | 46 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 296665 |
| 5° | 283072 |
| 10° | 269334 |
| 15° | 262135 |
| 20° | 252465 |
| 25° | 238925 |
| 30° | 222237 |
| 35° | 186689 |
| 40° | 120311 |
| 45° | 55913 |
| 50° | 14669 |
| 55° | 3670 |
| 60° | 3684 |
| 65° | 3113 |
| 70° | 3077 |
| 75° | 3050 |
| 80° | 3031 |
| 85° | 3019 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55913 cd/sqm



TEST NUMBER: P1302643

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CD1MMS_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 120.4 | 8.1 |
| 10°-20° | 324.5 | 21.7 |
| 20°-30° | 453.3 | 30.3 |
| 30°-40° | 420.3 | 28.1 |
| 40°-50° | 150.7 | 10.1 |
| 50°-60° | 12.8 | 0.9 |
| 60°-70° | 6.4 | 0.4 |
| 70°-80° | 4.1 | 0.3 |
| 80°-90° | 1.6 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 898.2 | 60.1 |
| 0°-40° | 1318.5 | 88.2 |
| 0°-60° | 1482.0 | 99.2 |
| 0°-90° | 1494.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1494.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1353 | |
| 5° | 1286 | 120 |
| 15° | 1155 | 324 |
| 25° | 988 | 453 |
| 35° | 697 | 420 |
| 45° | 180 | 151 |
| 55° | 10 | 13 |
| 65° | 6 | 6 |
| 75° | 4 | 4 |
| 85° | 1 | 2 |
| 90° | 0 | |



TEST NUMBER: P1302643
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3CD1MMS_3000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1352.9 |
| 2.5° | 1332.6 |
| 5° | 1286.0 |
| 7.5° | 1243.1 |
| 10° | 1209.6 |
| 12.5° | 1182.2 |
| 15° | 1154.7 |
| 17.5° | 1121.3 |
| 20° | 1081.9 |
| 22.5° | 1036.5 |
| 25° | 987.5 |
| 27.5° | 937.4 |
| 30° | 877.7 |
| 32.5° | 801.2 |
| 35° | 697.4 |
| 37.5° | 564.8 |
| 40° | 420.3 |
| 42.5° | 286.6 |
| 45° | 180.3 |
| 47.5° | 100.3 |
| 50° | 43.0 |
| 52.5° | 14.3 |
| 55° | 9.6 |
| 57.5° | 8.4 |
| 60° | 8.4 |
| 62.5° | 7.2 |
| 65° | 6.0 |
| 67.5° | 6.0 |
| 70° | 4.8 |
| 72.5° | 4.8 |
| 75° | 3.6 |
| 77.5° | 3.6 |
| 80° | 2.4 |
| 82.5° | 2.4 |
| 85° | 1.2 |
| 87.5° | 1.2 |
| 90° | 0.0 |

(END OF REPORT)