

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302657

Luminaire Tested: P3AS17R70W2N902750DE010 E3D1LI\_2700K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302657  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R70W2N902750DE010 E3D1LI\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI ,  
E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1291.0 lumens  
Efficiency: N/A  
Efficacy: 66.5 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302657  
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1LI\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1302657

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1LI\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	251033
5°	236693
10°	224445
15°	220410
20°	212445
25°	200262
30°	198841
35°	173170
40°	112010
45°	52936
50°	7403
55°	612
60°	482
65°	571
70°	321
75°	424
80°	631
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 52936 cd/sqm



TEST NUMBER: P1302657

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1LI\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.4	7.8
10°-20°	272.6	21.1
20°-30°	385.7	29.9
30°-40°	387.6	30.0
40°-50°	139.4	10.8
50°-60°	3.8	0.3
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	758.8	58.8
0°-40°	1146.4	88.8
0°-60°	1289.5	99.9
0°-90°	1291.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1291.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1145	
5°	1075	100
15°	971	273
25°	828	386
35°	647	388
45°	171	139
55°	2	4
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P1302657

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1LI\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1144.8
1°	1141.6
2°	1131.5
3°	1115.6
4°	1095.5
5°	1075.3
6°	1056.2
7°	1041.4
8°	1028.1
9°	1017.5
10°	1008.0
11°	1000.0
12°	992.6
13°	985.2
14°	978.3
15°	970.9
16°	961.8
17°	952.3
18°	940.6
19°	926.3
20°	910.4
21°	892.9
22°	875.4
23°	858.4
24°	842.0
25°	827.7
26°	817.6
27°	809.7
28°	803.3
29°	795.9
30°	785.3
31°	769.9
32°	748.2
32.5°	736.0
33°	719.5
34°	687.2
35°	646.9
36°	602.3
37°	552.0
37.5°	528.6
38°	496.8
39°	440.1
40°	391.3
42.5°	270.9
45°	170.7



TEST NUMBER: P1302657

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1LI\_2700K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	91.7
50°	21.7
52.5°	2.7
55°	1.6
57.5°	1.6
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)