

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302667

Luminaire Tested: P3AS17R70W2N902750DE010 E3D1WH_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902750DE010 E3D1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1291.0 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302667
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1302667
 CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79		
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	251033
5°	236693
10°	224445
15°	220410
20°	212445
25°	200262
30°	198841
35°	173170
40°	112010
45°	52936
50°	7403
55°	612
60°	482
65°	571
70°	321
75°	424
80°	631
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 52936 cd/sqm



TEST NUMBER: P1302667

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.4	7.8
10°-20°	272.6	21.1
20°-30°	385.7	29.9
30°-40°	387.6	30.0
40°-50°	139.4	10.8
50°-60°	3.8	0.3
60°-70°	0.9	0.1
70°-80°	0.5	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	758.8	58.8
0°-40°	1146.4	88.8
0°-60°	1289.5	99.9
0°-90°	1291.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1291.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1145	
5°	1075	100
15°	971	273
25°	828	386
35°	647	388
45°	171	139
55°	2	4
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P1302667
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1144.8
1°	1141.6
2°	1131.5
3°	1115.6
4°	1095.5
5°	1075.3
6°	1056.2
7°	1041.4
8°	1028.1
9°	1017.5
10°	1008.0
11°	1000.0
12°	992.6
13°	985.2
14°	978.3
15°	970.9
16°	961.8
17°	952.3
18°	940.6
19°	926.3
20°	910.4
21°	892.9
22°	875.4
23°	858.4
24°	842.0
25°	827.7
26°	817.6
27°	809.7
28°	803.3
29°	795.9
30°	785.3
31°	769.9
32°	748.2
32.5°	736.0
33°	719.5
34°	687.2
35°	646.9
36°	602.3
37°	552.0
37.5°	528.6
38°	496.8
39°	440.1
40°	391.3
42.5°	270.9
45°	170.7



TEST NUMBER: P1302667
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	91.7
50°	21.7
52.5°	2.7
55°	1.6
57.5°	1.6
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)