

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302784

Luminaire Tested: P3AS17R70W2N902765DE010 E3D1H_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902765DE010 E3D1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1424.1 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302784
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3D1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302784

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3D1H_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	276886
5°	261082
10°	247557
15°	243112
20°	234334
25°	220900
30°	219325
35°	190998
40°	123546
45°	58394
50°	8187
55°	688
60°	526
65°	623
70°	385
75°	508
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 58394 cd/sqm



TEST NUMBER: P1302784

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3D1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.8	7.8
10°-20°	300.7	21.1
20°-30°	425.4	29.9
30°-40°	427.5	30.0
40°-50°	153.8	10.8
50°-60°	4.2	0.3
60°-70°	1.0	0.1
70°-80°	0.6	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	836.9	58.8
0°-40°	1264.5	88.8
0°-60°	1422.4	99.9
0°-90°	1424.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1424.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1263	
5°	1186	111
15°	1071	301
25°	913	425
35°	714	428
45°	188	154
55°	2	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1302784

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3D1H_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1262.7
1°	1259.2
2°	1248.1
3°	1230.5
4°	1208.3
5°	1186.1
6°	1165.0
7°	1148.7
8°	1134.0
9°	1122.3
10°	1111.8
11°	1103.0
12°	1094.9
13°	1086.7
14°	1079.1
15°	1070.9
16°	1060.9
17°	1050.4
18°	1037.5
19°	1021.7
20°	1004.2
21°	984.9
22°	965.6
23°	946.9
24°	928.8
25°	913.0
26°	901.8
27°	893.1
28°	886.1
29°	877.9
30°	866.2
31°	849.2
32°	825.2
32.5°	811.8
33°	793.7
34°	758.0
35°	713.5
36°	664.4
37°	608.8
37.5°	583.1
38°	548.0
39°	485.4
40°	431.6
42.5°	298.9
45°	188.3



TEST NUMBER: P1302784

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3D1H_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	101.2
50°	24.0
52.5°	2.9
55°	1.8
57.5°	1.8
60°	1.2
62.5°	1.2
65°	1.2
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)