

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300667

Luminaire Tested: P3AS17R35W2N902765DE010 E3DLD1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300667
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R35W2N902765DE010 E3DLD1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 6500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 478.0 lumens
Efficiency: N/A
Efficacy: 24.6 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300667
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1300667

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.2	9.5
10°-20°	110.1	23.0
20°-30°	126.2	26.4
30°-40°	103.0	21.5
40°-50°	51.9	10.9
50°-60°	19.3	4.0
60°-70°	12.9	2.7
70°-80°	7.2	1.5
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.5	58.9
0°-40°	384.5	80.4
0°-60°	455.7	95.3
0°-90°	478.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	478.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	498	
5°	486	45
15°	396	110
25°	275	126
35°	166	103
45°	66	52
55°	20	19
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1300667

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	497.9
1°	497.4
2°	496.2
3°	493.8
4°	490.3
5°	485.5
6°	479.6
7°	473.7
8°	466.0
9°	458.4
10°	449.5
11°	440.1
12°	430.0
13°	418.8
14°	407.0
15°	395.8
17.5°	365.6
20°	334.9
22.5°	303.6
25°	275.3
27.5°	247.5
30°	220.3
32.5°	193.2
35°	166.0
37.5°	138.8
40°	112.2
42.5°	87.4
45°	65.6
47.5°	47.3
50°	32.5
52.5°	23.6
55°	20.1
57.5°	18.3
60°	16.5
62.5°	14.8
65°	13.0
67.5°	11.2
70°	10.0
72.5°	8.3
75°	6.5
77.5°	5.3
80°	4.1
82.5°	3.0
85°	1.8
87.5°	1.2



TEST NUMBER: P1300667
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)