

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302837

Luminaire Tested: P3AS17R70W2N902765DE010 E3DL1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902765DE010 E3DL1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 778.0 lumens
Efficiency: N/A
Efficacy: 40.1 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302837
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DL1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1302837

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DL1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | | | 92 |
| 2 | 106 | 101 | 97 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 90 | 93 | 90 | 88 | 90 | 88 | 86 | 84 | | | 84 |
| 3 | 100 | 93 | 88 | 83 | 98 | 92 | 87 | 83 | 89 | 85 | 81 | 87 | 83 | 80 | 84 | 81 | 79 | 77 | | | 77 |
| 4 | 95 | 86 | 80 | 76 | 93 | 85 | 80 | 75 | 83 | 78 | 74 | 81 | 77 | 73 | 79 | 76 | 73 | 71 | | | 71 |
| 5 | 89 | 80 | 74 | 69 | 88 | 79 | 73 | 69 | 78 | 72 | 68 | 76 | 71 | 68 | 74 | 70 | 67 | 65 | | | 65 |
| 6 | 85 | 75 | 68 | 64 | 83 | 74 | 68 | 64 | 73 | 67 | 63 | 71 | 66 | 63 | 70 | 65 | 62 | 61 | | | 61 |
| 7 | 80 | 70 | 64 | 59 | 79 | 69 | 63 | 59 | 68 | 62 | 58 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | 56 |
| 8 | 76 | 66 | 59 | 55 | 75 | 65 | 59 | 55 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 52 | | | 52 |
| 9 | 72 | 62 | 55 | 51 | 71 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 58 | 54 | 50 | 49 | | | 49 |
| 10 | 69 | 58 | 52 | 48 | 67 | 58 | 52 | 48 | 57 | 51 | 48 | 56 | 51 | 48 | 55 | 51 | 47 | 46 | | | 46 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 182485 |
| 5° | 179132 |
| 10° | 168912 |
| 15° | 153304 |
| 20° | 134085 |
| 25° | 113111 |
| 30° | 92622 |
| 35° | 71849 |
| 40° | 51411 |
| 45° | 32562 |
| 50° | 16238 |
| 55° | 9940 |
| 60° | 8552 |
| 65° | 7887 |
| 70° | 6924 |
| 75° | 6439 |
| 80° | 5430 |
| 85° | 5535 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 32562 cd/sqm



TEST NUMBER: P1302837

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DL1WH_2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 75.9 | 9.8 |
| 10°-20° | 187.9 | 24.2 |
| 20°-30° | 214.0 | 27.5 |
| 30°-40° | 167.3 | 21.5 |
| 40°-50° | 82.2 | 10.6 |
| 50°-60° | 25.3 | 3.2 |
| 60°-70° | 15.0 | 1.9 |
| 70°-80° | 8.0 | 1.0 |
| 80°-90° | 2.4 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 477.8 | 61.4 |
| 0°-40° | 645.2 | 82.9 |
| 0°-60° | 752.7 | 96.7 |
| 0°-90° | 778.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 778.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 832 | |
| 5° | 814 | 76 |
| 15° | 675 | 188 |
| 25° | 468 | 214 |
| 35° | 268 | 167 |
| 45° | 105 | 82 |
| 55° | 26 | 25 |
| 65° | 15 | 15 |
| 75° | 8 | 8 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P1302837
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DL1WH_2700K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 832.2 |
| 2.5° | 827.9 |
| 5° | 813.8 |
| 7.5° | 791.1 |
| 10° | 758.6 |
| 12.5° | 720.7 |
| 15° | 675.3 |
| 17.5° | 626.6 |
| 20° | 574.6 |
| 22.5° | 520.5 |
| 25° | 467.5 |
| 27.5° | 415.6 |
| 30° | 365.8 |
| 32.5° | 316.0 |
| 35° | 268.4 |
| 37.5° | 222.9 |
| 40° | 179.6 |
| 42.5° | 139.6 |
| 45° | 105.0 |
| 47.5° | 73.6 |
| 50° | 47.6 |
| 52.5° | 31.4 |
| 55° | 26.0 |
| 57.5° | 22.7 |
| 60° | 19.5 |
| 62.5° | 17.3 |
| 65° | 15.2 |
| 67.5° | 13.0 |
| 70° | 10.8 |
| 72.5° | 8.7 |
| 75° | 7.6 |
| 77.5° | 6.5 |
| 80° | 4.3 |
| 82.5° | 3.2 |
| 85° | 2.2 |
| 87.5° | 1.1 |
| 90° | 0.0 |

(END OF REPORT)