

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302853

Luminaire Tested: P3AS17R70W2N902765DE010 E3DLP1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302853
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902765DE010 E3DLP1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 425.0 lumens
Efficiency: N/A
Efficacy: 21.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302853
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302853
 CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99685
5°	97865
10°	92272
15°	83746
20°	73250
25°	61794
30°	50590
35°	39244
40°	28081
45°	17769
50°	8870
55°	5429
60°	4649
65°	4307
70°	3783
75°	3474
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17769 cd/sqm



TEST NUMBER: P1302853

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	9.8
10°-20°	102.6	24.2
20°-30°	116.9	27.5
30°-40°	91.4	21.5
40°-50°	44.9	10.6
50°-60°	13.8	3.2
60°-70°	8.2	1.9
70°-80°	4.3	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.0	61.4
0°-40°	352.4	82.9
0°-60°	411.1	96.7
0°-90°	425.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	425.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	455	
5°	445	41
15°	369	103
25°	255	117
35°	147	91
45°	57	45
55°	14	14
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1302853
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1GPH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	454.6
2.5°	452.3
5°	444.6
7.5°	432.2
10°	414.4
12.5°	393.7
15°	368.9
17.5°	342.3
20°	313.9
22.5°	284.4
25°	255.4
27.5°	227.0
30°	199.8
32.5°	172.6
35°	146.6
37.5°	121.8
40°	98.1
42.5°	76.3
45°	57.3
47.5°	40.2
50°	26.0
52.5°	17.1
55°	14.2
57.5°	12.4
60°	10.6
62.5°	9.5
65°	8.3
67.5°	7.1
70°	5.9
72.5°	4.7
75°	4.1
77.5°	3.5
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)