

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300707

Luminaire Tested: P3AS17R35W2N902765DE010 E3DLP1H\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300707  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R35W2N902765DE010 E3DLP1H\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 90CRI ,  
E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 786.0 lumens  
Efficiency: N/A  
Efficacy: 40.5 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300707  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1H\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1300707

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1H\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80				80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74				74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69				69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65				65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61				61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57				57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51				51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	252633
5°	246422
10°	225291
15°	191216
20°	151376
25°	114490
30°	83355
35°	56376
40°	34636
45°	19878
50°	11974
55°	9711
60°	8508
65°	7524
70°	6219
75°	6185
80°	6061
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19878 cd/sqm



TEST NUMBER: P1300707

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1H\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.5	13.2
10°-20°	232.2	29.5
20°-30°	217.2	27.6
30°-40°	133.0	16.9
40°-50°	52.4	6.7
50°-60°	23.1	2.9
60°-70°	14.3	1.8
70°-80°	7.7	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.9	70.3
0°-40°	685.9	87.3
0°-60°	761.4	96.9
0°-90°	786.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	786.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1152	
5°	1120	103
15°	842	232
25°	473	217
35°	211	133
45°	64	52
55°	25	23
65°	14	14
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1300707  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1H\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1152.1
1°	1153.3
2°	1149.7
3°	1142.5
4°	1131.6
5°	1119.5
6°	1103.7
7°	1085.6
8°	1063.8
9°	1039.6
10°	1011.8
11°	982.7
12°	951.2
13°	917.4
14°	879.8
15°	842.3
17.5°	745.5
20°	648.7
22.5°	555.5
25°	473.2
27.5°	397.0
30°	329.2
32.5°	266.3
35°	210.6
37.5°	161.0
40°	121.0
42.5°	87.1
45°	64.1
47.5°	46.0
50°	35.1
52.5°	29.0
55°	25.4
57.5°	21.8
60°	19.4
62.5°	16.9
65°	14.5
67.5°	12.1
70°	9.7
72.5°	8.5
75°	7.3
77.5°	6.1
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2



TEST NUMBER: P1300707  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1H\_4000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)