

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302875

Luminaire Tested: P3AS17R70W2N902765DE010 E3DLP1WH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1302875  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R70W2N902765DE010 E3DLP1WH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1220.0 lumens  
Efficiency: N/A  
Efficacy: 62.9 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1302875  
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1WH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1302875

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1WH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84			84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77			77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70			70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44			44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	236187
5°	233347
10°	226605
15°	217005
20°	203274
25°	184680
30°	159518
35°	127127
40°	92602
45°	60875
50°	28519
55°	8793
60°	8508
65°	8198
70°	7758
75°	8218
80°	7703
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 60875 cd/sqm



TEST NUMBER: P1302875

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1WH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.8	8.2
10°-20°	267.5	21.9
20°-30°	347.7	28.5
30°-40°	295.0	24.2
40°-50°	152.1	12.5
50°-60°	29.3	2.4
60°-70°	15.9	1.3
70°-80°	9.8	0.8
80°-90°	2.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.1	58.6
0°-40°	1010.1	82.8
0°-60°	1191.6	97.7
0°-90°	1220.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1220.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1077	
5°	1060	100
15°	956	268
25°	763	348
35°	475	295
45°	196	152
55°	23	29
65°	16	16
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1302875  
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1WH\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1077.1
2.5°	1073.4
5°	1060.1
7.5°	1040.7
10°	1017.7
12.5°	988.6
15°	955.9
17.5°	915.9
20°	871.1
22.5°	820.2
25°	763.3
27.5°	699.1
30°	630.0
32.5°	553.7
35°	474.9
37.5°	397.4
40°	323.5
42.5°	254.4
45°	196.3
47.5°	144.2
50°	83.6
52.5°	36.3
55°	23.0
57.5°	21.8
60°	19.4
62.5°	18.2
65°	15.8
67.5°	14.5
70°	12.1
72.5°	10.9
75°	9.7
77.5°	7.3
80°	6.1
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)