

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246825

Luminaire Tested: P3A13R209024DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R209024DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1083.0 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246825
CATALOG NUMBER: P3A13R209024DE010 E3CD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1246825

CATALOG NUMBER: P3A13R209024DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	99	98	98
2	112	109	106	104	110	108	105	103	104	103	101	102	100	99	99	98	97	99	98	97
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	97	96	95
4	107	102	99	96	105	101	98	96	99	97	94	97	95	93	96	94	92	96	94	92
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	94	92	91
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	93	90	89
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	91	89	87
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	89	87	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	88	86	84
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	86	84	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1682014
5°	1459935
10°	902076
15°	313328
20°	96212
25°	34018
30°	12584
35°	5059
40°	2691
45°	1054
50°	580
55°	650
60°	746
65°	467
70°	577
75°	763
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1054 cd/sqm



TEST NUMBER: P1246825
 CATALOG NUMBER: P3A13R209024DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	550.4	50.8
10°-20°	436.7	40.3
20°-30°	75.6	7.0
30°-40°	13.7	1.3
40°-50°	3.1	0.3
50°-60°	1.5	0.1
60°-70°	1.0	0.1
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1062.8	98.1
0°-40°	1076.6	99.4
0°-60°	1081.2	99.8
0°-90°	1083.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1083.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7671	
5°	6632	550
15°	1380	437
25°	141	76
35°	19	14
45°	3	3
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1246825
CATALOG NUMBER: P3A13R209024DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7670.6
1°	7633.8
2°	7488.0
3°	7254.0
4°	6979.7
5°	6632.5
6°	6234.7
7°	5771.8
8°	5244.6
9°	4652.3
10°	4051.3
12.5°	2555.5
15°	1380.2
17.5°	737.2
20°	412.3
22.5°	235.7
25°	140.6
27.5°	85.7
30°	49.7
32.5°	29.1
35°	18.9
37.5°	12.9
40°	9.4
42.5°	6.0
45°	3.4
47.5°	1.7
50°	1.7
52.5°	1.7
55°	1.7
57.5°	1.7
60°	1.7
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)