

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246870

Luminaire Tested: P3A13R259024DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246870  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R259024DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 550.0 lumens  
Efficiency: N/A  
Efficacy: 37.7 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246870  
CATALOG NUMBER: P3A13R259024DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1246870  
 CATALOG NUMBER: P3A13R259024DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	199677
5°	191569
10°	167821
15°	134893
20°	103656
25°	78416
30°	56667
35°	37638
40°	22814
45°	13304
50°	8494
55°	6881
60°	6008
65°	5344
70°	4424
75°	4321
80°	3283
85°	4277

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13304 cd/sqm



TEST NUMBER: P1246870  
 CATALOG NUMBER: P3A13R259024DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.2	14.4
10°-20°	164.3	29.9
20°-30°	148.6	27.0
30°-40°	89.3	16.2
40°-50°	35.5	6.4
50°-60°	16.3	3.0
60°-70°	10.0	1.8
70°-80°	5.3	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	392.1	71.3
0°-40°	481.4	87.5
0°-60°	533.2	96.9
0°-90°	550.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	550.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	911	
5°	870	79
15°	594	164
25°	324	149
35°	141	89
45°	43	35
55°	18	16
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1246870  
CATALOG NUMBER: P3A13R259024DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	910.6
1°	910.6
2°	906.3
3°	896.9
4°	884.9
5°	870.3
6°	851.5
7°	830.0
8°	805.1
9°	780.3
10°	753.7
11°	722.8
12°	691.1
13°	659.4
14°	627.7
15°	594.2
17.5°	515.3
20°	444.2
22.5°	379.9
25°	324.1
27.5°	271.8
30°	223.8
32.5°	180.1
35°	140.6
37.5°	107.2
40°	79.7
42.5°	58.3
45°	42.9
47.5°	32.6
50°	24.9
52.5°	20.6
55°	18.0
57.5°	15.4
60°	13.7
62.5°	11.1
65°	10.3
67.5°	8.6
70°	6.9
72.5°	6.0
75°	5.1
77.5°	4.3
80°	2.6
82.5°	1.7
85°	1.7
87.5°	0.9



TEST NUMBER: P1246870  
CATALOG NUMBER: P3A13R259024DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)