

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301138

Luminaire Tested: P3AS17R45W2N902750DE010 E3DLD1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301138
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R45W2N902750DE010 E3DLD1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 515.0 lumens
Efficiency: N/A
Efficacy: 26.5 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301138
CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLD1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1301138

CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLD1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75			75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58			58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54			54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50			50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47			47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44			44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109202
5°	107264
10°	101490
15°	92554
20°	81860
25°	71085
30°	61022
35°	50835
40°	37900
45°	23196
50°	10746
55°	8411
60°	8070
65°	7368
70°	6860
75°	6524
80°	5935
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23196 cd/sqm



TEST NUMBER: P1301138

CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLD1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	8.8
10°-20°	113.5	22.0
20°-30°	134.9	26.2
30°-40°	117.2	22.8
40°-50°	58.8	11.4
50°-60°	20.4	4.0
60°-70°	14.3	2.8
70°-80°	8.0	1.5
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.9	57.1
0°-40°	411.1	79.8
0°-60°	490.3	95.2
0°-90°	515.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	515.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	498	
5°	487	46
15°	408	114
25°	294	135
35°	190	117
45°	75	59
55°	22	20
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1301138
CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	498.0
2.5°	495.6
5°	487.3
7.5°	474.2
10°	455.8
12.5°	433.3
15°	407.7
17.5°	379.3
20°	350.8
22.5°	321.7
25°	293.8
27.5°	267.1
30°	241.0
32.5°	216.0
35°	189.9
37.5°	162.0
40°	132.4
42.5°	103.3
45°	74.8
47.5°	49.3
50°	31.5
52.5°	24.3
55°	22.0
57.5°	20.2
60°	18.4
62.5°	16.6
65°	14.2
67.5°	12.5
70°	10.7
72.5°	8.9
75°	7.7
77.5°	5.9
80°	4.7
82.5°	3.6
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)