

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247022

Luminaire Tested: P3A13R559024DE010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1247022  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R559024DE010 E3CB1MMS  
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1141.0 lumens  
Efficiency: N/A  
Efficacy: 78.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247022

CATALOG NUMBER: P3A13R559024DE010 E3CB1MMS

### Luminous Intensity Polar Plot



TEST NUMBER: P1247022

CATALOG NUMBER: P3A13R559024DE010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 |  | 101 | 100 | 99  |  | 98  |
| 2   | 109 | 104 | 101 | 98  | 107 | 103 | 99  | 96  | 100 | 97  | 94  |  | 97  | 94  | 92  |  | 94  |
| 3   | 104 | 98  | 94  | 90  | 102 | 97  | 93  | 89  | 94  | 91  | 88  |  | 92  | 89  | 86  |  | 90  |
| 4   | 99  | 92  | 87  | 84  | 98  | 91  | 87  | 83  | 89  | 85  | 82  |  | 87  | 84  | 81  |  | 85  |
| 5   | 95  | 87  | 82  | 78  | 93  | 86  | 81  | 78  | 85  | 80  | 77  |  | 83  | 79  | 76  |  | 82  |
| 6   | 91  | 83  | 77  | 73  | 89  | 82  | 77  | 73  | 80  | 76  | 72  |  | 79  | 75  | 72  |  | 78  |
| 7   | 87  | 78  | 73  | 69  | 85  | 78  | 72  | 69  | 76  | 72  | 68  |  | 75  | 71  | 68  |  | 74  |
| 8   | 83  | 74  | 69  | 65  | 82  | 74  | 68  | 65  | 73  | 68  | 65  |  | 72  | 67  | 64  |  | 71  |
| 9   | 79  | 71  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 68  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  |  | 65  | 61  | 58  |  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 316466 |
| 5°  | 313514 |
| 10° | 326113 |
| 15° | 321591 |
| 20° | 296546 |
| 25° | 241296 |
| 30° | 146554 |
| 35° | 50728  |
| 40° | 14484  |
| 45° | 6915   |
| 50° | 2934   |
| 55° | 1300   |
| 60° | 1491   |
| 65° | 1349   |
| 70° | 1090   |
| 75° | 1440   |
| 80° | 1137   |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6915 cd/sqm

TEST NUMBER: P1247022

CATALOG NUMBER: P3A13R559024DE010 E3CB1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 137.7  | 12.1      |
| 10°-20°   | 393.7  | 34.5      |
| 20°-30°   | 438.9  | 38.5      |
| 30°-40°   | 143.6  | 12.6      |
| 40°-50°   | 18.9   | 1.7       |
| 50°-60°   | 4.0    | 0.3       |
| 60°-70°   | 2.3    | 0.2       |
| 70°-80°   | 1.5    | 0.1       |
| 80°-90°   | 0.4    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 970.3  | 85.0      |
| 0°-40°    | 1113.9 | 97.6      |
| 0°-60°    | 1136.8 | 99.6      |
| 0°-90°    | 1141.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1141.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1443 |      |
| 5°  | 1424 | 138  |
| 15° | 1417 | 394  |
| 25° | 997  | 439  |
| 35° | 190  | 144  |
| 45° | 22   | 19   |
| 55° | 3    | 4    |
| 65° | 3    | 2    |
| 75° | 2    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1247022

CATALOG NUMBER: P3A13R559024DE010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1443.2 |
| 2.5°  | 1432.9 |
| 5°    | 1424.3 |
| 7.5°  | 1444.9 |
| 10°   | 1464.6 |
| 12.5° | 1454.3 |
| 15°   | 1416.6 |
| 17.5° | 1356.6 |
| 20°   | 1270.8 |
| 22.5° | 1152.5 |
| 25°   | 997.3  |
| 27.5° | 800.1  |
| 30°   | 578.8  |
| 32.5° | 355.0  |
| 35°   | 189.5  |
| 37.5° | 96.0   |
| 40°   | 50.6   |
| 42.5° | 32.6   |
| 45°   | 22.3   |
| 47.5° | 15.4   |
| 50°   | 8.6    |
| 52.5° | 5.1    |
| 55°   | 3.4    |
| 57.5° | 3.4    |
| 60°   | 3.4    |
| 62.5° | 2.6    |
| 65°   | 2.6    |
| 67.5° | 1.7    |
| 70°   | 1.7    |
| 72.5° | 1.7    |
| 75°   | 1.7    |
| 77.5° | 0.9    |
| 80°   | 0.9    |
| 82.5° | 0.9    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)