

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301161

Luminaire Tested: P3AS17R45W2N902750DE010 E3DLD1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301161  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R45W2N902750DE010 E3DLD1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 939.0 lumens  
Efficiency: N/A  
Efficacy: 48.4 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301161  
CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLD1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301161

CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLD1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75			75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58			58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54			54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50			50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47			47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44			44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	199085
5°	195553
10°	185056
15°	168764
20°	149230
25°	129612
30°	111258
35°	92702
40°	69072
45°	42299
50°	19581
55°	15292
60°	14692
65°	13490
70°	12502
75°	11946
80°	10986
85°	8051

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 42299 cd/sqm



TEST NUMBER: P1301161

CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLD1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.0	8.8
10°-20°	207.0	22.0
20°-30°	245.9	26.2
30°-40°	213.7	22.8
40°-50°	107.2	11.4
50°-60°	37.2	4.0
60°-70°	26.1	2.8
70°-80°	14.6	1.6
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.9	57.1
0°-40°	749.6	79.8
0°-60°	894.0	95.2
0°-90°	939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	939.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	908	
5°	888	83
15°	743	207
25°	536	246
35°	346	214
45°	136	107
55°	40	37
65°	26	26
75°	14	15
85°	3	4
90°	0	

TEST NUMBER: P1301161

CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLD1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	907.9
2.5°	903.6
5°	888.4
7.5°	864.6
10°	831.1
12.5°	790.0
15°	743.4
17.5°	691.5
20°	639.5
22.5°	586.5
25°	535.7
27.5°	487.0
30°	439.4
32.5°	393.9
35°	346.3
37.5°	295.4
40°	241.3
42.5°	188.3
45°	136.4
47.5°	89.8
50°	57.4
52.5°	44.4
55°	40.0
57.5°	36.8
60°	33.5
62.5°	30.3
65°	26.0
67.5°	22.7
70°	19.5
72.5°	16.2
75°	14.1
77.5°	10.8
80°	8.7
82.5°	6.5
85°	3.2
87.5°	2.2
90°	0.0

(END OF REPORT)