

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301167

Luminaire Tested: P3AS17R45W2N902750DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301167
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R45W2N902750DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 422.0 lumens
Efficiency: N/A
Efficacy: 21.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301167
CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301167
 CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLP1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64			
7	83	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125692
5°	122826
10°	113313
15°	98525
20°	80950
25°	62979
30°	46513
35°	32712
40°	20438
45°	11071
50°	5970
55°	5161
60°	4605
65°	3943
70°	3398
75°	3474
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11071 cd/sqm



TEST NUMBER: P1301167

CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.7	12.2
10°-20°	120.0	28.4
20°-30°	119.1	28.2
30°-40°	76.7	18.2
40°-50°	29.6	7.0
50°-60°	12.0	2.8
60°-70°	7.6	1.8
70°-80°	4.1	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.8	68.9
0°-40°	367.5	87.1
0°-60°	409.1	96.9
0°-90°	422.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	422.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	573	
5°	558	52
15°	434	120
25°	260	119
35°	122	77
45°	36	30
55°	14	12
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1301167
CATALOG NUMBER: P3AS17R45W2N902750DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	573.2
2.5°	570.3
5°	558.0
7.5°	537.0
10°	508.9
12.5°	473.8
15°	434.0
17.5°	390.7
20°	346.9
22.5°	302.4
25°	260.3
27.5°	220.5
30°	183.7
32.5°	151.5
35°	122.2
37.5°	95.9
40°	71.4
42.5°	51.5
45°	35.7
47.5°	24.0
50°	17.5
52.5°	14.6
55°	13.5
57.5°	11.7
60°	10.5
62.5°	8.8
65°	7.6
67.5°	6.4
70°	5.3
72.5°	4.7
75°	4.1
77.5°	2.9
80°	2.3
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)