

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247358

Luminaire Tested: P3A17R459024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R459024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 483.0 lumens
Efficiency: N/A
Efficacy: 22.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247358
CATALOG NUMBER: P3A17R459024DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1247358

CATALOG NUMBER: P3A17R459024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102404
5°	100594
10°	95189
15°	86811
20°	76773
25°	66657
30°	57224
35°	47676
40°	35524
45°	21739
50°	10064
55°	7875
60°	7587
65°	6953
70°	6411
75°	6100
80°	5683
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21739 cd/sqm



TEST NUMBER: P1247358
 CATALOG NUMBER: P3A17R459024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	8.8
10°-20°	106.5	22.0
20°-30°	126.5	26.2
30°-40°	109.9	22.8
40°-50°	55.1	11.4
50°-60°	19.1	4.0
60°-70°	13.4	2.8
70°-80°	7.5	1.5
80°-90°	2.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	275.7	57.1
0°-40°	385.6	79.8
0°-60°	459.8	95.2
0°-90°	483.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	483.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	467	
5°	457	43
15°	382	106
25°	276	126
35°	178	110
45°	70	55
55°	21	19
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1247358
CATALOG NUMBER: P3A17R459024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	467.0
2.5°	464.8
5°	457.0
7.5°	444.7
10°	427.5
12.5°	406.3
15°	382.4
17.5°	355.7
20°	329.0
22.5°	301.7
25°	275.5
27.5°	250.5
30°	226.0
32.5°	202.6
35°	178.1
37.5°	152.0
40°	124.1
42.5°	96.9
45°	70.1
47.5°	46.2
50°	29.5
52.5°	22.8
55°	20.6
57.5°	18.9
60°	17.3
62.5°	15.6
65°	13.4
67.5°	11.7
70°	10.0
72.5°	8.3
75°	7.2
77.5°	5.6
80°	4.5
82.5°	3.3
85°	1.7
87.5°	1.1
90°	0.0

(END OF REPORT)