

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247515

Luminaire Tested: P3A20R159024D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R159024D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1886.0 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247515

CATALOG NUMBER: P3A20R159024D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1247515

CATALOG NUMBER: P3A20R159024D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	106		104	103	103		101	100	100
2	113	110	107	105		111	108	106	104		105	103	101		102	101	99		99	98	97
3	110	106	103	100		108	105	102	100		102	100	98		100	98	97		98	97	95
4	107	103	100	97		106	102	99	97		100	97	95		98	96	94		97	95	93
5	105	100	97	94		104	99	96	94		98	95	93		96	94	92		95	93	92
6	103	98	94	92		102	97	94	92		96	93	91		95	92	91		94	92	90
7	101	96	92	90		100	95	92	90		94	91	89		93	91	89		92	90	89
8	99	94	90	88		98	93	90	88		92	90	88		92	89	87		91	89	87
9	97	92	89	87		97	92	89	86		91	88	86		90	88	86		90	87	86
10	96	90	87	85		95	90	87	85		89	87	85		89	86	85		88	86	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3665934
5°	3072411
10°	1447223
15°	436325
20°	161457
25°	62762
30°	23396
35°	7174
40°	2548
45°	1395
50°	1023
55°	1147
60°	1316
65°	778
70°	962
75°	1271
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1395 cd/sqm

TEST NUMBER: P1247515

CATALOG NUMBER: P3A20R159024D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1079.1	57.2
10°-20°	641.4	34.0
20°-30°	134.7	7.1
30°-40°	21.7	1.2
40°-50°	3.7	0.2
50°-60°	2.7	0.1
60°-70°	1.7	0.1
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1855.3	98.4
0°-40°	1877.0	99.5
0°-60°	1883.4	99.9
0°-90°	1886.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1886.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16718	
5°	13958	###
15°	1922	641
25°	259	135
35°	27	22
45°	4	4
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1247515

CATALOG NUMBER: P3A20R159024D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	16718.0
1°	16665.8
2°	16400.4
3°	15869.6
4°	15091.2
5°	13958.0
6°	12626.5
7°	11104.1
8°	9650.3
9°	8004.1
10°	6499.6
12.5°	3507.0
15°	1922.0
17.5°	1125.8
20°	691.9
22.5°	423.5
25°	259.4
27.5°	156.6
30°	92.4
32.5°	52.2
35°	26.8
37.5°	14.9
40°	8.9
42.5°	6.0
45°	4.5
47.5°	3.0
50°	3.0
52.5°	3.0
55°	3.0
57.5°	3.0
60°	3.0
62.5°	1.5
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)