

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247550

Luminaire Tested: P3A20R209024D010 E3D1LI

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1247550  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R209024D010 E3D1LI  
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1869.0 lumens  
Efficiency: N/A  
Efficacy: 64.9 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1247550

CATALOG NUMBER: P3A20R209024D010 E3D1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1247550

CATALOG NUMBER: P3A20R209024D010 E3D1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 114 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 |  | 104 | 103 | 102 |  | 100 |
| 2   | 112 | 109 | 106 | 104 | 110 | 107 | 105 | 103 | 104 | 102 | 101 |  | 101 | 100 | 98  |  | 99  |
| 3   | 109 | 105 | 102 | 99  | 107 | 104 | 101 | 98  | 101 | 99  | 97  |  | 99  | 97  | 95  |  | 97  |
| 4   | 106 | 101 | 98  | 95  | 105 | 100 | 97  | 95  | 99  | 96  | 94  |  | 97  | 95  | 93  |  | 95  |
| 5   | 104 | 98  | 95  | 92  | 102 | 98  | 94  | 92  | 96  | 93  | 91  |  | 95  | 92  | 90  |  | 93  |
| 6   | 101 | 96  | 92  | 89  | 100 | 95  | 92  | 89  | 94  | 91  | 89  |  | 93  | 90  | 88  |  | 92  |
| 7   | 99  | 93  | 90  | 87  | 98  | 93  | 89  | 87  | 92  | 89  | 86  |  | 91  | 88  | 86  |  | 90  |
| 8   | 97  | 91  | 87  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  |  | 89  | 86  | 84  |  | 88  |
| 9   | 95  | 89  | 85  | 83  | 94  | 89  | 85  | 83  | 88  | 85  | 83  |  | 87  | 84  | 83  |  | 87  |
| 10  | 93  | 87  | 84  | 81  | 92  | 87  | 83  | 81  | 86  | 83  | 81  |  | 86  | 83  | 81  |  | 85  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2835124 |
| 5°  | 2387051 |
| 10° | 1490932 |
| 15° | 557393  |
| 20° | 191327  |
| 25° | 79747   |
| 30° | 37550   |
| 35° | 16811   |
| 40° | 7958    |
| 45° | 4093    |
| 50° | 1501    |
| 55° | 268     |
| 60° | 307     |
| 65° | 363     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4093 cd/sqm

TEST NUMBER: P1247550

CATALOG NUMBER: P3A20R209024D010 E3D1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 901.8  | 48.3      |
| 10°-20°   | 742.8  | 39.7      |
| 20°-30°   | 168.8  | 9.0       |
| 30°-40°   | 43.0   | 2.3       |
| 40°-50°   | 10.8   | 0.6       |
| 50°-60°   | 1.3    | 0.1       |
| 60°-70°   | 0.4    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1813.4 | 97.0      |
| 0°-40°    | 1856.4 | 99.3      |
| 0°-60°    | 1868.5 | 100.0     |
| 0°-90°    | 1869.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1869.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 12929 |      |
| 5°  | 10844 | 902  |
| 15° | 2455  | 743  |
| 25° | 330   | 169  |
| 35° | 63    | 43   |
| 45° | 13    | 11   |
| 55° | 1     | 1    |
| 65° | 1     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P1247550

CATALOG NUMBER: P3A20R209024D010 E3D1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 12929.2 |
| 1°    | 12819.6 |
| 2°    | 12496.6 |
| 3°    | 12033.3 |
| 4°    | 11464.8 |
| 5°    | 10844.4 |
| 6°    | 10153.1 |
| 7°    | 9390.2  |
| 8°    | 8500.1  |
| 9°    | 7618.1  |
| 10°   | 6695.9  |
| 11°   | 5714.5  |
| 12°   | 4734.5  |
| 13°   | 3904.4  |
| 14°   | 3110.8  |
| 15°   | 2455.3  |
| 16°   | 1938.0  |
| 17°   | 1528.7  |
| 18°   | 1228.4  |
| 19°   | 998.9   |
| 20°   | 819.9   |
| 21°   | 685.4   |
| 22°   | 572.2   |
| 23°   | 475.7   |
| 24°   | 396.8   |
| 25°   | 329.6   |
| 27.5° | 215.6   |
| 30°   | 148.3   |
| 32.5° | 91.3    |
| 35°   | 62.8    |
| 37.5° | 40.2    |
| 40°   | 27.8    |
| 42.5° | 19.0    |
| 45°   | 13.2    |
| 47.5° | 8.8     |
| 50°   | 4.4     |
| 52.5° | 2.2     |
| 55°   | 0.7     |
| 57.5° | 0.7     |
| 60°   | 0.7     |
| 62.5° | 0.7     |
| 65°   | 0.7     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |

TEST NUMBER: P1247550  
CATALOG NUMBER: P3A20R209024D010 E3D1LI

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)