

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301426

Luminaire Tested: P3AS17R50W2N902750DE010 E3DL1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301426  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R50W2N902750DE010 E3DL1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1218.0 lumens  
Efficiency: N/A  
Efficacy: 62.8 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301426  
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DL1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301426  
 CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DL1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76	76	76	76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67	67	67	67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57	57	57	57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54	54	54	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	387798
5°	379968
10°	355905
15°	318617
20°	268123
25°	204641
30°	132982
35°	78862
40°	45571
45°	22824
50°	8494
55°	6614
60°	6184
65°	5604
70°	5578
75°	5507
80°	5430
85°	5535

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22824 cd/sqm



TEST NUMBER: P1301426

CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DL1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.6	13.2
10°-20°	388.1	31.9
20°-30°	380.8	31.3
30°-40°	191.8	15.8
40°-50°	60.6	5.0
50°-60°	15.7	1.3
60°-70°	11.1	0.9
70°-80°	6.9	0.6
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	929.5	76.3
0°-40°	1121.4	92.1
0°-60°	1197.7	98.3
0°-90°	1218.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1218.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1768	
5°	1726	161
15°	1404	388
25°	846	381
35°	295	192
45°	74	61
55°	17	16
65°	11	11
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1301426  
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DL1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1768.5
2.5°	1757.6
5°	1726.2
7.5°	1669.9
10°	1598.4
12.5°	1506.4
15°	1403.5
17.5°	1284.4
20°	1149.0
22.5°	1002.8
25°	845.8
27.5°	679.0
30°	525.2
32.5°	395.3
35°	294.6
37.5°	217.7
40°	159.2
42.5°	112.6
45°	73.6
47.5°	42.2
50°	24.9
52.5°	18.4
55°	17.3
57.5°	15.2
60°	14.1
62.5°	13.0
65°	10.8
67.5°	9.7
70°	8.7
72.5°	7.6
75°	6.5
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)