

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301480

Luminaire Tested: P3AS17R50W2N902750DE010 E3DLP1MW\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301480  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R50W2N902750DE010 E3DLP1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 890.0 lumens  
Efficiency: N/A  
Efficacy: 45.9 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301480  
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLP1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301480  
 CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLP1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68			
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56			
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	258861
5°	251881
10°	232260
15°	204269
20°	170908
25°	135516
30°	99433
35°	68369
40°	43453
45°	24282
50°	13134
55°	11049
60°	9517
65°	8769
70°	7694
75°	7117
80°	6061
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24282 cd/sqm



TEST NUMBER: P1301480

CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLP1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.0	11.9
10°-20°	249.2	28.0
20°-30°	254.9	28.6
30°-40°	161.6	18.2
40°-50°	64.3	7.2
50°-60°	26.1	2.9
60°-70°	16.7	1.9
70°-80°	8.5	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.1	68.6
0°-40°	771.8	86.7
0°-60°	862.1	96.9
0°-90°	890.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	890.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1180	
5°	1144	106
15°	900	249
25°	560	255
35°	255	162
45°	78	64
55°	29	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1301480  
CATALOG NUMBER: P3AS17R50W2N902750DE010 E3DLP1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1180.5
2.5°	1172.0
5°	1144.3
7.5°	1101.0
10°	1043.1
12.5°	974.5
15°	899.8
17.5°	817.9
20°	732.4
22.5°	646.8
25°	560.1
27.5°	473.4
30°	392.7
32.5°	320.4
35°	255.4
37.5°	200.0
40°	151.8
42.5°	112.0
45°	78.3
47.5°	53.0
50°	38.5
52.5°	32.5
55°	28.9
57.5°	25.3
60°	21.7
62.5°	19.3
65°	16.9
67.5°	14.5
70°	12.0
72.5°	9.6
75°	8.4
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)