

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247782

Luminaire Tested: P3A20R609024D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247782
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R609024D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1786.0 lumens
Efficiency: N/A
Efficacy: 62.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247782

CATALOG NUMBER: P3A20R609024D010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1247782

CATALOG NUMBER: P3A20R609024D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	96	91	88		93	89	86		91	87	85		88	86	84
4	98	91	85	81		96	90	85	81		88	83	80		86	82	79		84	81	78
5	93	85	80	75		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	70		77	72	69		75	72	69
7	85	76	70	66		83	75	69	65		74	69	65		72	68	65		71	67	64
8	81	71	65	61		79	71	65	61		70	65	61		69	64	61		68	64	61
9	77	67	62	58		76	67	61	58		66	61	57		65	61	57		64	60	57
10	73	64	58	54		72	63	58	54		63	58	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	467967
5°	441755
10°	430275
15°	420434
20°	390914
25°	349472
30°	266927
35°	154110
40°	59798
45°	24933
50°	5492
55°	841
60°	658
65°	363
70°	449
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24933 cd/sqm

TEST NUMBER: P1247782

CATALOG NUMBER: P3A20R609024D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	10.6
10°-20°	515.9	28.9
20°-30°	646.1	36.2
30°-40°	361.2	20.2
40°-50°	68.7	3.8
50°-60°	3.5	0.2
60°-70°	0.8	0.0
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1351.5	75.7
0°-40°	1712.7	95.9
0°-60°	1784.9	99.9
0°-90°	1786.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1786.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2134	
5°	2007	189
15°	1852	516
25°	1444	646
35°	576	361
45°	80	69
55°	2	4
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1247782

CATALOG NUMBER: P3A20R609024D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2134.1
1°	2125.3
2°	2097.5
3°	2064.6
4°	2034.0
5°	2006.9
6°	1986.5
7°	1968.9
8°	1955.8
9°	1943.4
10°	1932.4
11°	1921.5
12°	1909.0
13°	1893.7
14°	1875.4
15°	1852.0
16°	1823.6
17°	1791.4
18°	1754.9
19°	1713.2
20°	1675.2
21°	1634.3
22°	1592.0
23°	1547.4
24°	1498.4
25°	1444.4
26°	1380.8
27°	1309.9
28°	1230.3
29°	1145.6
30°	1054.2
31°	962.2
32°	867.2
32.5°	815.3
33°	768.6
34°	671.4
35°	575.7
36°	489.5
37°	398.2
37.5°	356.5
38°	315.6
39°	254.2
40°	208.9
42.5°	127.1
45°	80.4



TEST NUMBER: P1247782

CATALOG NUMBER: P3A20R609024D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	44.6
50°	16.1
52.5°	3.7
55°	2.2
57.5°	1.5
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)