

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1247810

Luminaire Tested: P3A20R659024D010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1247810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R659024D010 E3D1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1844.0 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1247810
CATALOG NUMBER: P3A20R659024D010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1247810

CATALOG NUMBER: P3A20R659024D010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75	75	75	75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	450644
5°	424124
10°	418741
15°	411353
20°	388370
25°	360456
30°	280195
35°	162088
40°	65322
45°	30050
50°	11701
55°	4549
60°	3903
65°	3891
70°	3847
75°	3813
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30050 cd/sqm



TEST NUMBER: P1247810
 CATALOG NUMBER: P3A20R659024D010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.2	9.9
10°-20°	506.0	27.4
20°-30°	662.4	35.9
30°-40°	383.7	20.8
40°-50°	82.1	4.5
50°-60°	13.4	0.7
60°-70°	7.4	0.4
70°-80°	4.4	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1351.5	73.3
0°-40°	1735.2	94.1
0°-60°	1830.7	99.3
0°-90°	1844.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1844.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2055	
5°	1927	183
15°	1812	506
25°	1490	662
35°	606	384
45°	97	82
55°	12	13
65°	8	7
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P1247810
CATALOG NUMBER: P3A20R659024D010 E3D1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2055.1
2.5°	1996.9
5°	1926.8
7.5°	1898.5
10°	1880.6
12.5°	1855.2
15°	1812.0
17.5°	1744.9
20°	1664.3
22.5°	1588.3
25°	1489.8
27.5°	1324.3
30°	1106.6
32.5°	857.5
35°	605.5
37.5°	383.3
40°	228.2
42.5°	143.2
45°	96.9
47.5°	62.6
50°	34.3
52.5°	16.4
55°	11.9
57.5°	10.4
60°	8.9
62.5°	8.9
65°	7.5
67.5°	6.0
70°	6.0
72.5°	4.5
75°	4.5
77.5°	3.0
80°	3.0
82.5°	1.5
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)