

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301581

Luminaire Tested: P3AS17R50W2N902765DE010 E3DL1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301581
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R50W2N902765DE010 E3DL1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 799.0 lumens
Efficiency: N/A
Efficacy: 41.2 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301581
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DL1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1301581

CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DL1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	11.9
10°-20°	223.7	28.0
20°-30°	228.8	28.6
30°-40°	145.1	18.2
40°-50°	57.8	7.2
50°-60°	23.4	2.9
60°-70°	15.0	1.9
70°-80°	7.7	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	547.7	68.5
0°-40°	692.8	86.7
0°-60°	774.0	96.9
0°-90°	799.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	799.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1060	
5°	1027	95
15°	808	224
25°	503	229
35°	229	145
45°	70	58
55°	26	23
65°	15	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1301581
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DL1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1059.8
2.5°	1052.2
5°	1027.3
7.5°	988.4
10°	936.5
12.5°	874.8
15°	807.8
17.5°	734.3
20°	657.5
22.5°	580.7
25°	502.8
27.5°	425.0
30°	352.5
32.5°	287.7
35°	229.3
37.5°	179.5
40°	136.3
42.5°	100.6
45°	70.3
47.5°	47.6
50°	34.6
52.5°	29.2
55°	26.0
57.5°	22.7
60°	19.5
62.5°	17.3
65°	15.1
67.5°	13.0
70°	10.8
72.5°	8.7
75°	7.6
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)