

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245614

Luminaire Tested: P3A02R159024DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R159024DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 132.0 lumens
Efficiency: N/A
Efficacy: 36.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245614

CATALOG NUMBER: P3A02R159024DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1245614

CATALOG NUMBER: P3A02R159024DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	73	78	75	72	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56925
5°	52608
10°	41994
15°	31737
20°	24152
25°	18412
30°	13192
35°	8620
40°	5267
45°	3194
50°	2115
55°	1644
60°	1403
65°	1245
70°	1090
75°	1101
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3194 cd/sqm

TEST NUMBER: P1245614

CATALOG NUMBER: P3A02R159024DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.2	16.0
10°-20°	39.1	29.6
20°-30°	34.8	26.4
30°-40°	20.6	15.6
40°-50°	8.4	6.4
50°-60°	3.9	3.0
60°-70°	2.4	1.8
70°-80°	1.3	1.0
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	95.0	72.0
0°-40°	115.6	87.6
0°-60°	128.0	97.0
0°-90°	132.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	132.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	239	21
15°	140	39
25°	76	35
35°	32	21
45°	10	8
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1245614

CATALOG NUMBER: P3A02R159024DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	259.6
1°	258.9
2°	257.0
3°	253.2
4°	246.7
5°	239.0
6°	230.6
7°	220.8
8°	210.5
9°	200.0
10°	188.6
12.5°	162.7
15°	139.8
17.5°	120.0
20°	103.5
22.5°	89.0
25°	76.1
27.5°	63.7
30°	52.1
32.5°	41.6
35°	32.2
37.5°	24.7
40°	18.4
42.5°	13.7
45°	10.3
47.5°	7.9
50°	6.2
52.5°	5.1
55°	4.3
57.5°	3.6
60°	3.2
62.5°	2.8
65°	2.4
67.5°	2.1
70°	1.7
72.5°	1.5
75°	1.3
77.5°	0.9
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)