

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301588

Luminaire Tested: P3AS17R50W2N902765DE010 E3DL1WMH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301588  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R50W2N902765DE010 E3DL1WMH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1343.0 lumens  
Efficiency: N/A  
Efficacy: 69.2 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301588  
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DL1WMH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301588

CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DL1WMH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 94  | 94  | 94  | 94  |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  | 95  | 93  | 91  | 93  | 91  | 89  | 87  | 87  | 87  | 87  |
| 3   | 103 | 97  | 92  | 88  | 101 | 95  | 91  | 87  | 93  | 89  | 86  | 90  | 87  | 84  | 88  | 85  | 83  | 82  | 82  | 82  | 82  |
| 4   | 98  | 91  | 85  | 81  | 96  | 90  | 85  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 84  | 80  | 78  | 76  | 76  | 76  | 76  |
| 5   | 93  | 85  | 80  | 75  | 92  | 84  | 79  | 75  | 83  | 78  | 74  | 81  | 77  | 74  | 79  | 76  | 73  | 72  | 72  | 72  | 72  |
| 6   | 89  | 80  | 75  | 71  | 88  | 80  | 74  | 70  | 78  | 73  | 70  | 77  | 73  | 69  | 75  | 72  | 69  | 67  | 67  | 67  | 67  |
| 7   | 85  | 76  | 70  | 66  | 84  | 75  | 70  | 66  | 74  | 69  | 66  | 73  | 69  | 65  | 72  | 68  | 65  | 64  | 64  | 64  | 64  |
| 8   | 81  | 72  | 66  | 62  | 80  | 71  | 66  | 62  | 70  | 65  | 62  | 69  | 65  | 62  | 68  | 64  | 61  | 60  | 60  | 60  | 60  |
| 9   | 78  | 68  | 63  | 59  | 76  | 68  | 62  | 59  | 67  | 62  | 59  | 66  | 62  | 58  | 65  | 61  | 58  | 57  | 57  | 57  | 57  |
| 10  | 74  | 65  | 59  | 56  | 73  | 65  | 59  | 56  | 64  | 59  | 55  | 63  | 58  | 55  | 62  | 58  | 55  | 54  | 54  | 54  | 54  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 427597 |
| 5°  | 418973 |
| 10° | 392444 |
| 15° | 351307 |
| 20° | 295636 |
| 25° | 225642 |
| 30° | 146630 |
| 35° | 86946  |
| 40° | 50237  |
| 45° | 25181  |
| 50° | 9381   |
| 55° | 7302   |
| 60° | 6798   |
| 65° | 6174   |
| 70° | 6155   |
| 75° | 6100   |
| 80° | 6061   |
| 85° | 6038   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25181 cd/sqm



TEST NUMBER: P1301588

CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DL1WMH\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 177.1  | 13.2      |
| 10°-20°   | 428.0  | 31.9      |
| 20°-30°   | 419.9  | 31.3      |
| 30°-40°   | 211.5  | 15.7      |
| 40°-50°   | 66.8   | 5.0       |
| 50°-60°   | 17.3   | 1.3       |
| 60°-70°   | 12.2   | 0.9       |
| 70°-80°   | 7.6    | 0.6       |
| 80°-90°   | 2.6    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1024.9 | 76.3      |
| 0°-40°    | 1236.4 | 92.1      |
| 0°-60°    | 1320.6 | 98.3      |
| 0°-90°    | 1343.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1343.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1950 |      |
| 5°  | 1903 | 177  |
| 15° | 1548 | 428  |
| 25° | 933  | 420  |
| 35° | 325  | 212  |
| 45° | 81   | 67   |
| 55° | 19   | 17   |
| 65° | 12   | 12   |
| 75° | 7    | 8    |
| 85° | 2    | 3    |
| 90° | 0    |      |



TEST NUMBER: P1301588  
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DL1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1950.0 |
| 2.5°  | 1938.0 |
| 5°    | 1903.4 |
| 7.5°  | 1841.3 |
| 10°   | 1762.5 |
| 12.5° | 1661.0 |
| 15°   | 1547.5 |
| 17.5° | 1416.2 |
| 20°   | 1266.9 |
| 22.5° | 1105.7 |
| 25°   | 932.6  |
| 27.5° | 748.7  |
| 30°   | 579.1  |
| 32.5° | 435.8  |
| 35°   | 324.8  |
| 37.5° | 240.0  |
| 40°   | 175.5  |
| 42.5° | 124.2  |
| 45°   | 81.2   |
| 47.5° | 46.6   |
| 50°   | 27.5   |
| 52.5° | 20.3   |
| 55°   | 19.1   |
| 57.5° | 16.7   |
| 60°   | 15.5   |
| 62.5° | 14.3   |
| 65°   | 11.9   |
| 67.5° | 10.7   |
| 70°   | 9.6    |
| 72.5° | 8.4    |
| 75°   | 7.2    |
| 77.5° | 6.0    |
| 80°   | 4.8    |
| 82.5° | 3.6    |
| 85°   | 2.4    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)