

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301598

Luminaire Tested: P3AS17R50W2N902765DE010 E3DLD1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R50W2N902765DE010 E3DLD1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 6500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 517.0 lumens
Efficiency: N/A
Efficacy: 26.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301598
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLD1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1301598

CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLD1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105057
5°	103522
10°	98929
15°	91624
20°	82350
25°	72391
30°	61554
35°	49925
40°	37499
45°	24158
50°	11462
55°	9022
60°	8552
65°	7939
70°	7181
75°	6524
80°	5935
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24158 cd/sqm



TEST NUMBER: P1301598

CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLD1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.1	8.5
10°-20°	112.5	21.8
20°-30°	136.7	26.4
30°-40°	116.0	22.4
40°-50°	60.2	11.6
50°-60°	21.7	4.2
60°-70°	15.0	2.9
70°-80°	8.2	1.6
80°-90°	2.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.3	56.7
0°-40°	409.3	79.2
0°-60°	491.2	95.0
0°-90°	517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	517.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	479	
5°	470	44
15°	404	113
25°	299	137
35°	186	116
45°	78	60
55°	24	22
65°	15	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1301598
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	479.1
2.5°	477.4
5°	470.3
7.5°	459.7
10°	444.3
12.5°	424.8
15°	403.6
17.5°	379.4
20°	352.9
22.5°	325.7
25°	299.2
27.5°	271.4
30°	243.1
32.5°	214.8
35°	186.5
37.5°	158.7
40°	131.0
42.5°	104.4
45°	77.9
47.5°	51.9
50°	33.6
52.5°	26.0
55°	23.6
57.5°	21.2
60°	19.5
62.5°	17.1
65°	15.3
67.5°	13.0
70°	11.2
72.5°	9.4
75°	7.7
77.5°	5.9
80°	4.7
82.5°	3.5
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)