

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301649

Luminaire Tested: P3AS17R50W2N902765DE010 E3DLP1MW\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301649  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R50W2N902765DE010 E3DLP1MW\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 895.0 lumens  
Efficiency: N/A  
Efficacy: 46.1 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301649  
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLP1MW\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301649  
 CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLP1MW\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79	79	79	79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73	73	73	73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68	68	68	68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64	64	64	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60	60	60	60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56	56	56	56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53	53	53	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50	50	50	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	260308
5°	253312
10°	233574
15°	205427
20°	171865
25°	136290
30°	99990
35°	68743
40°	43682
45°	24406
50°	13236
55°	11125
60°	9561
65°	8821
70°	7758
75°	7202
80°	6061
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24406 cd/sqm



TEST NUMBER: P1301649

CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLP1MW\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.6	11.9
10°-20°	250.6	28.0
20°-30°	256.3	28.6
30°-40°	162.5	18.2
40°-50°	64.7	7.2
50°-60°	26.2	2.9
60°-70°	16.8	1.9
70°-80°	8.6	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.6	68.6
0°-40°	776.1	86.7
0°-60°	867.0	96.9
0°-90°	895.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	895.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1187	
5°	1151	107
15°	905	251
25°	563	256
35°	257	163
45°	79	65
55°	29	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1301649  
CATALOG NUMBER: P3AS17R50W2N902765DE010 E3DLP1MW\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1187.1
2.5°	1178.6
5°	1150.8
7.5°	1107.2
10°	1049.0
12.5°	980.0
15°	904.9
17.5°	822.5
20°	736.5
22.5°	650.5
25°	563.3
27.5°	476.1
30°	394.9
32.5°	322.2
35°	256.8
37.5°	201.1
40°	152.6
42.5°	112.7
45°	78.7
47.5°	53.3
50°	38.8
52.5°	32.7
55°	29.1
57.5°	25.4
60°	21.8
62.5°	19.4
65°	17.0
67.5°	14.5
70°	12.1
72.5°	9.7
75°	8.5
77.5°	6.1
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)