

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301681

Luminaire Tested: P3AS17R55W2N902750DE010 E3CD1MB_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R55W2N902750DE010 E3CD1MB_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1589.0 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301681
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CD1MB_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301681

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CD1MB_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	12.1
10°-20°	548.3	34.5
20°-30°	611.3	38.5
30°-40°	200.0	12.6
40°-50°	26.4	1.7
50°-60°	5.6	0.4
60°-70°	3.3	0.2
70°-80°	2.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1351.3	85.0
0°-40°	1551.3	97.6
0°-60°	1583.2	99.6
0°-90°	1589.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1589.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2010	
5°	1984	192
15°	1973	548
25°	1389	611
35°	264	200
45°	31	26
55°	5	6
65°	4	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1301681
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3CD1MB_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2009.8
2.5°	1995.5
5°	1983.6
7.5°	2012.2
10°	2039.7
12.5°	2025.4
15°	1972.8
17.5°	1889.2
20°	1769.8
22.5°	1605.0
25°	1388.8
27.5°	1114.2
30°	806.1
32.5°	494.4
35°	263.9
37.5°	133.7
40°	70.5
42.5°	45.4
45°	31.0
47.5°	21.5
50°	11.9
52.5°	7.2
55°	4.8
57.5°	4.8
60°	4.8
62.5°	3.6
65°	3.6
67.5°	2.4
70°	2.4
72.5°	2.4
75°	2.4
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)