

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245702

Luminaire Tested: P3A02R309024DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R309024DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 139.0 lumens
Efficiency: N/A
Efficacy: 38.6 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245702
CATALOG NUMBER: P3A02R309024DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1245702
 CATALOG NUMBER: P3A02R309024DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	68	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47496
5°	46027
10°	41460
15°	34302
20°	26556
25°	19912
30°	14458
35°	9637
40°	5925
45°	3473
50°	2149
55°	1720
60°	1491
65°	1245
70°	1090
75°	1101
80°	758
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3473 cd/sqm



TEST NUMBER: P1245702
 CATALOG NUMBER: P3A02R309024DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.2	13.8
10°-20°	41.6	29.9
20°-30°	37.9	27.2
30°-40°	22.9	16.5
40°-50°	9.2	6.6
50°-60°	4.1	2.9
60°-70°	2.5	1.8
70°-80°	1.3	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	98.7	71.0
0°-40°	121.6	87.5
0°-60°	134.8	97.0
0°-90°	139.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	139.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	217	
5°	209	19
15°	151	42
25°	82	38
35°	36	23
45°	11	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1245702
CATALOG NUMBER: P3A02R309024DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	216.6
1°	216.4
2°	215.5
3°	214.0
4°	211.9
5°	209.1
6°	205.6
7°	202.0
8°	197.2
9°	191.8
10°	186.2
11°	179.8
12°	172.9
13°	166.0
14°	158.4
15°	151.1
17.5°	131.9
20°	113.8
22.5°	97.0
25°	82.3
27.5°	69.0
30°	57.1
32.5°	46.1
35°	36.0
37.5°	27.6
40°	20.7
42.5°	15.1
45°	11.2
47.5°	8.4
50°	6.3
52.5°	5.0
55°	4.5
57.5°	3.9
60°	3.4
62.5°	2.8
65°	2.4
67.5°	2.2
70°	1.7
72.5°	1.5
75°	1.3
77.5°	1.1
80°	0.6
82.5°	0.4
85°	0.4
87.5°	0.2



TEST NUMBER: P1245702
CATALOG NUMBER: P3A02R309024DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)