

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301717

Luminaire Tested: P3AS17R55W2N902750DE010 E3D1WMH_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301717
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R55W2N902750DE010 E3D1WMH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1564.0 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301717
CATALOG NUMBER: P3AS17R55W2N902750DE010 E3D1WMH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1301717

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3D1WMH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95			95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84			84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79			79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75			75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71			71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67			67
8	83	75	69	66	82	74	69	66	73	69	65	72	68	65	71	68	65	63			63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60			60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57			57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	453538
5°	437485
10°	453120
15°	446745
20°	413456
25°	334374
30°	200385
35°	67914
40°	18721
45°	8280
50°	2422
55°	459
60°	263
65°	311
70°	385
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8280 cd/sqm



TEST NUMBER: P1301717

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3D1WMH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.3	12.3
10°-20°	547.9	35.0
20°-30°	609.0	38.9
30°-40°	189.6	12.1
40°-50°	22.8	1.5
50°-60°	1.8	0.1
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1349.2	86.3
0°-40°	1538.8	98.4
0°-60°	1563.3	100.0
0°-90°	1564.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1564.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2068	
5°	1988	192
15°	1968	548
25°	1382	609
35°	254	190
45°	27	23
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1301717

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3D1WMH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2068.3
1°	2060.6
2°	2040.4
3°	2015.4
4°	1992.9
5°	1987.5
6°	1993.5
7°	2005.9
8°	2020.2
9°	2031.5
10°	2035.0
11°	2032.7
12°	2023.2
13°	2008.3
14°	1991.1
15°	1967.9
16°	1941.2
17°	1907.3
18°	1869.3
19°	1823.5
20°	1771.8
21°	1713.0
22°	1643.5
23°	1566.8
24°	1478.9
25°	1382.0
26°	1275.7
27°	1162.8
28°	1042.2
29°	918.0
30°	791.4
31°	664.3
32°	540.1
32.5°	484.8
33°	427.8
34°	331.0
35°	253.7
36°	193.1
37°	143.2
37.5°	122.4
38°	106.4
39°	80.8
40°	65.4
42.5°	41.6
45°	26.7



TEST NUMBER: P1301717

CATALOG NUMBER: P3AS17R55W2N902750DE010 E3D1WMH_3500K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	16.0
50°	7.1
52.5°	2.4
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)