

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245845

Luminaire Tested: P3A02R559024DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1245845  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A02R559024DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 156.0 lumens  
Efficiency: N/A  
Efficacy: 43.3 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1245845  
CATALOG NUMBER: P3A02R559024DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1245845  
 CATALOG NUMBER: P3A02R559024DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79				79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55				55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52				52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49				49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	42431
5°	41382
10°	38454
15°	34257
20°	29099
25°	23493
30°	17901
35°	12742
40°	8416
45°	4993
50°	2934
55°	1797
60°	1579
65°	1453
70°	1218
75°	1101
80°	1137
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4993 cd/sqm



TEST NUMBER: P1245845  
 CATALOG NUMBER: P3A02R559024DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	17.5	11.2
10°-20°	41.8	26.8
20°-30°	44.3	28.4
30°-40°	29.9	19.2
40°-50°	13.1	8.4
50°-60°	4.7	3.0
60°-70°	2.8	1.8
70°-80°	1.5	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	103.6	66.4
0°-40°	133.5	85.6
0°-60°	151.4	97.0
0°-90°	156.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	156.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	194	
5°	188	17
15°	151	42
25°	97	44
35°	48	30
45°	16	13
55°	5	5
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1245845  
CATALOG NUMBER: P3A02R559024DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	193.5
2.5°	192.0
5°	188.0
7.5°	181.3
10°	172.7
12.5°	162.5
15°	150.9
17.5°	138.0
20°	124.7
22.5°	110.8
25°	97.1
27.5°	83.6
30°	70.7
32.5°	58.5
35°	47.6
37.5°	37.7
40°	29.4
42.5°	22.1
45°	16.1
47.5°	11.8
50°	8.6
52.5°	6.0
55°	4.7
57.5°	4.3
60°	3.6
62.5°	3.2
65°	2.8
67.5°	2.4
70°	1.9
72.5°	1.7
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)