

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245919

Luminaire Tested: P3A02R709024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R709024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 106.0 lumens
Efficiency: N/A
Efficacy: 29.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245919
CATALOG NUMBER: P3A02R709024DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1245919
 CATALOG NUMBER: P3A02R709024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20525
5°	20273
10°	19683
15°	18865
20°	17665
25°	16041
30°	13850
35°	11056
40°	8044
45°	5303
50°	2490
55°	765
60°	746
65°	726
70°	705
75°	678
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5303 cd/sqm



TEST NUMBER: P1245919
 CATALOG NUMBER: P3A02R709024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.7	8.2
10°-20°	23.2	21.9
20°-30°	30.2	28.5
30°-40°	25.6	24.2
40°-50°	13.2	12.5
50°-60°	2.6	2.4
60°-70°	1.4	1.3
70°-80°	0.8	0.8
80°-90°	0.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	62.1	58.6
0°-40°	87.8	82.8
0°-60°	103.5	97.7
0°-90°	106.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	106.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	94	
5°	92	9
15°	83	23
25°	66	30
35°	41	26
45°	17	13
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1245919
CATALOG NUMBER: P3A02R709024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	93.6
2.5°	93.3
5°	92.1
7.5°	90.4
10°	88.4
12.5°	85.9
15°	83.1
17.5°	79.6
20°	75.7
22.5°	71.3
25°	66.3
27.5°	60.7
30°	54.7
32.5°	48.1
35°	41.3
37.5°	34.5
40°	28.1
42.5°	22.1
45°	17.1
47.5°	12.5
50°	7.3
52.5°	3.2
55°	2.0
57.5°	1.9
60°	1.7
62.5°	1.6
65°	1.4
67.5°	1.3
70°	1.1
72.5°	0.9
75°	0.8
77.5°	0.6
80°	0.5
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)