

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426011

Luminaire Tested: P3A02RH9024DE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02RH9024DE010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 2400K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 103.0 lumens
Efficiency: N/A
Efficacy: 28.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426011

CATALOG NUMBER: P3A02RH9024DE010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426011

CATALOG NUMBER: P3A02RH9024DE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	92	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	76	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49667
5°	45498
10°	39768
15°	34892
20°	17642
25°	8783
30°	7951
35°	6050
40°	4237
45°	2853
50°	1842
55°	1223
60°	833
65°	675
70°	385
75°	339
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2853 cd/sqm

TEST NUMBER: P1426011

CATALOG NUMBER: P3A02RH9024DE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.8	18.3
10°-20°	38.9	37.8
20°-30°	19.0	18.4
30°-40°	14.2	13.8
40°-50°	7.3	7.1
50°-60°	3.0	2.9
60°-70°	1.2	1.2
70°-80°	0.4	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	76.7	74.5
0°-40°	90.9	88.3
0°-60°	101.2	98.3
0°-90°	103.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	103.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	226	
5°	207	19
15°	154	39
25°	36	19
35°	23	14
45°	9	7
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426011

CATALOG NUMBER: P3A02RH9024DE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	226.5
2.5°	221.4
5°	206.7
7.5°	191.0
10°	178.6
12.5°	169.3
15°	153.7
17.5°	119.9
20°	75.6
22.5°	44.9
25°	36.3
27.5°	33.5
30°	31.4
32.5°	27.5
35°	22.6
37.5°	18.5
40°	14.8
42.5°	11.8
45°	9.2
47.5°	7.1
50°	5.4
52.5°	4.1
55°	3.2
57.5°	2.6
60°	1.9
62.5°	1.5
65°	1.3
67.5°	0.9
70°	0.6
72.5°	0.6
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)