

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301828

Luminaire Tested: P3AS17R55W2N902765DE010 E3CD1MB\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301828  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R55W2N902765DE010 E3CD1MB\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,  
E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1441.0 lumens  
Efficiency: N/A  
Efficacy: 74.3 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301828  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3CD1MB\_2700K

### Luminous Intensity Polar Plot







TEST NUMBER: P1301828

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3CD1MB\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	173.9	12.1
10°-20°	497.2	34.5
20°-30°	554.3	38.5
30°-40°	181.3	12.6
40°-50°	23.9	1.7
50°-60°	5.0	0.3
60°-70°	2.9	0.2
70°-80°	1.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1225.5	85.0
0°-40°	1406.8	97.6
0°-60°	1435.8	99.6
0°-90°	1441.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1441.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1823	
5°	1799	174
15°	1789	497
25°	1260	554
35°	239	181
45°	28	24
55°	4	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1301828  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3CD1MB\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1822.6
2.5°	1809.6
5°	1798.8
7.5°	1824.8
10°	1849.7
12.5°	1836.7
15°	1789.1
17.5°	1713.3
20°	1605.0
22.5°	1455.5
25°	1259.5
27.5°	1010.4
30°	731.0
32.5°	448.3
35°	239.3
37.5°	121.3
40°	63.9
42.5°	41.2
45°	28.2
47.5°	19.5
50°	10.8
52.5°	6.5
55°	4.3
57.5°	4.3
60°	4.3
62.5°	3.2
65°	3.2
67.5°	2.2
70°	2.2
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)