

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246035

Luminaire Tested: P3A05R209024DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R209024DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 557.9 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246035
CATALOG NUMBER: P3A05R209024DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1246035

CATALOG NUMBER: P3A05R209024DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	97	96	93
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	92	96	94	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	91	94	92	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	88	93	90	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	86	91	89	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85	89	87	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	83	88	86	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	87	84	82	82	87	84	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	866641
5°	752210
10°	464788
15°	161431
20°	49564
25°	17517
30°	6482
35°	2597
40°	1403
45°	558
50°	307
55°	344
60°	395
65°	208
70°	256
75°	339
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 558 cd/sqm



TEST NUMBER: P1246035
 CATALOG NUMBER: P3A05R209024DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.6	50.8
10°-20°	225.0	40.3
20°-30°	39.0	7.0
30°-40°	7.1	1.3
40°-50°	1.6	0.3
50°-60°	0.8	0.1
60°-70°	0.5	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	547.6	98.1
0°-40°	554.7	99.4
0°-60°	557.1	99.9
0°-90°	557.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	557.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3952	
5°	3417	284
15°	711	225
25°	72	39
35°	10	7
45°	2	2
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1246035
CATALOG NUMBER: P3A05R209024DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3952.2
1°	3933.2
2°	3858.1
3°	3737.5
4°	3596.2
5°	3417.3
6°	3212.4
7°	2973.9
8°	2702.2
9°	2397.0
10°	2087.4
12.5°	1316.7
15°	711.1
17.5°	379.8
20°	212.4
22.5°	121.5
25°	72.4
27.5°	44.2
30°	25.6
32.5°	15.0
35°	9.7
37.5°	6.6
40°	4.9
42.5°	3.1
45°	1.8
47.5°	0.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)