

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301924

Luminaire Tested: P3AS17R55W2N902765DE010 E3DLD1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301924
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R55W2N902765DE010 E3DLD1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 916.0 lumens
Efficiency: N/A
Efficacy: 47.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301924
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1301924
 CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1LI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 100 | 98 | 99 | 97 | 95 | 95 | 94 | 93 | 91 | | |
| 2 | 105 | 100 | 95 | 91 | 103 | 98 | 93 | 90 | 94 | 91 | 88 | 91 | 88 | 86 | 89 | 86 | 84 | 82 | | |
| 3 | 99 | 91 | 85 | 81 | 97 | 90 | 84 | 80 | 87 | 82 | 79 | 85 | 81 | 77 | 82 | 79 | 76 | 74 | | |
| 4 | 93 | 84 | 77 | 72 | 91 | 83 | 77 | 72 | 80 | 75 | 71 | 78 | 74 | 70 | 76 | 73 | 69 | 68 | | |
| 5 | 87 | 77 | 71 | 66 | 85 | 76 | 70 | 65 | 75 | 69 | 65 | 73 | 68 | 64 | 71 | 67 | 64 | 62 | | |
| 6 | 82 | 72 | 65 | 60 | 80 | 71 | 64 | 60 | 69 | 64 | 59 | 68 | 63 | 59 | 66 | 62 | 58 | 57 | | |
| 7 | 77 | 67 | 60 | 55 | 76 | 66 | 59 | 55 | 65 | 59 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 52 | | |
| 8 | 73 | 62 | 55 | 51 | 72 | 62 | 55 | 51 | 60 | 55 | 50 | 59 | 54 | 50 | 58 | 53 | 50 | 48 | | |
| 9 | 69 | 58 | 51 | 47 | 68 | 58 | 51 | 47 | 57 | 51 | 47 | 56 | 50 | 46 | 55 | 50 | 46 | 45 | | |
| 10 | 65 | 55 | 48 | 44 | 64 | 54 | 48 | 44 | 53 | 47 | 43 | 52 | 47 | 43 | 52 | 47 | 43 | 42 | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 172223 |
| 5° | 170041 |
| 10° | 163324 |
| 15° | 152759 |
| 20° | 139359 |
| 25° | 124338 |
| 30° | 108751 |
| 35° | 90346 |
| 40° | 71219 |
| 45° | 48315 |
| 50° | 29509 |
| 55° | 15292 |
| 60° | 14253 |
| 65° | 13490 |
| 70° | 12502 |
| 75° | 11014 |
| 80° | 10986 |
| 85° | 8051 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 48315 cd/sqm



TEST NUMBER: P1301924

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1LI_2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 72.4 | 7.9 |
| 10°-20° | 188.1 | 20.5 |
| 20°-30° | 235.5 | 25.7 |
| 30°-40° | 210.2 | 23.0 |
| 40°-50° | 123.1 | 13.4 |
| 50°-60° | 42.5 | 4.6 |
| 60°-70° | 25.7 | 2.8 |
| 70°-80° | 14.3 | 1.6 |
| 80°-90° | 4.1 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 496.1 | 54.2 |
| 0°-40° | 706.3 | 77.1 |
| 0°-60° | 871.9 | 95.2 |
| 0°-90° | 916.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 916.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 785 | |
| 5° | 772 | 72 |
| 15° | 673 | 188 |
| 25° | 514 | 236 |
| 35° | 338 | 210 |
| 45° | 156 | 123 |
| 55° | 40 | 43 |
| 65° | 26 | 26 |
| 75° | 13 | 14 |
| 85° | 3 | 4 |
| 90° | 0 | |



TEST NUMBER: P1301924
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1LI_2700K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 785.4 |
| 2.5° | 781.1 |
| 5° | 772.5 |
| 7.5° | 755.1 |
| 10° | 733.5 |
| 12.5° | 706.5 |
| 15° | 672.9 |
| 17.5° | 637.2 |
| 20° | 597.2 |
| 22.5° | 556.1 |
| 25° | 513.9 |
| 27.5° | 471.7 |
| 30° | 429.5 |
| 32.5° | 384.1 |
| 35° | 337.5 |
| 37.5° | 292.1 |
| 40° | 248.8 |
| 42.5° | 202.3 |
| 45° | 155.8 |
| 47.5° | 119.0 |
| 50° | 86.5 |
| 52.5° | 56.3 |
| 55° | 40.0 |
| 57.5° | 35.7 |
| 60° | 32.5 |
| 62.5° | 29.2 |
| 65° | 26.0 |
| 67.5° | 22.7 |
| 70° | 19.5 |
| 72.5° | 16.2 |
| 75° | 13.0 |
| 77.5° | 10.8 |
| 80° | 8.7 |
| 82.5° | 5.4 |
| 85° | 3.2 |
| 87.5° | 2.2 |
| 90° | 0.0 |

(END OF REPORT)