

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301941

Luminaire Tested: P3AS17R55W2N902765DE010 E3DLD1WH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301941  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R55W2N902765DE010 E3DLD1WH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 6500K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1020.0 lumens  
Efficiency: N/A  
Efficacy: 52.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301941  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1WH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301941  
 CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1WH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 |  | 100 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 100 | 98  | 99  | 97  | 95  | 95  | 94  | 93  |  | 91  |
| 2   | 105 | 100 | 95  | 91  | 103 | 98  | 93  | 90  | 94  | 91  | 88  | 91  | 88  | 86  | 89  | 86  | 84  |  | 82  |
| 3   | 99  | 91  | 85  | 81  | 97  | 90  | 84  | 80  | 87  | 82  | 79  | 85  | 81  | 77  | 82  | 79  | 76  |  | 74  |
| 4   | 93  | 84  | 77  | 72  | 91  | 83  | 77  | 72  | 80  | 75  | 71  | 78  | 74  | 70  | 76  | 73  | 69  |  | 68  |
| 5   | 87  | 77  | 71  | 66  | 85  | 76  | 70  | 65  | 75  | 69  | 65  | 73  | 68  | 64  | 71  | 67  | 64  |  | 62  |
| 6   | 82  | 72  | 65  | 60  | 80  | 71  | 64  | 60  | 69  | 64  | 59  | 68  | 63  | 59  | 66  | 62  | 58  |  | 57  |
| 7   | 77  | 67  | 60  | 55  | 76  | 66  | 59  | 55  | 65  | 59  | 54  | 63  | 58  | 54  | 62  | 57  | 54  |  | 52  |
| 8   | 73  | 62  | 55  | 51  | 72  | 62  | 55  | 51  | 60  | 55  | 50  | 59  | 54  | 50  | 58  | 53  | 50  |  | 48  |
| 9   | 69  | 58  | 51  | 47  | 68  | 58  | 51  | 47  | 57  | 51  | 47  | 56  | 50  | 46  | 55  | 50  | 46  |  | 45  |
| 10  | 65  | 55  | 48  | 44  | 64  | 54  | 48  | 44  | 53  | 47  | 43  | 52  | 47  | 43  | 52  | 47  | 43  |  | 42  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 191783 |
| 5°  | 189346 |
| 10° | 181871 |
| 15° | 170103 |
| 20° | 155180 |
| 25° | 138443 |
| 30° | 121107 |
| 35° | 100626 |
| 40° | 79320  |
| 45° | 53804  |
| 50° | 32886  |
| 55° | 17051  |
| 60° | 15832  |
| 65° | 14995  |
| 70° | 13913  |
| 75° | 12285  |
| 80° | 12123  |
| 85° | 9057   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 53804 cd/sqm



TEST NUMBER: P1301941

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1WH\_6500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 80.7   | 7.9       |
| 10°-20°   | 209.4  | 20.5      |
| 20°-30°   | 262.3  | 25.7      |
| 30°-40°   | 234.1  | 23.0      |
| 40°-50°   | 137.1  | 13.4      |
| 50°-60°   | 47.4   | 4.6       |
| 60°-70°   | 28.6   | 2.8       |
| 70°-80°   | 15.9   | 1.6       |
| 80°-90°   | 4.6    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 552.4  | 54.2      |
| 0°-40°    | 786.5  | 77.1      |
| 0°-60°    | 971.0  | 95.2      |
| 0°-90°    | 1020.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1020.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 875 |      |
| 5°  | 860 | 81   |
| 15° | 749 | 209  |
| 25° | 572 | 262  |
| 35° | 376 | 234  |
| 45° | 174 | 137  |
| 55° | 45  | 47   |
| 65° | 29  | 29   |
| 75° | 14  | 16   |
| 85° | 4   | 5    |
| 90° | 0   |      |



TEST NUMBER: P1301941  
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DLD1WH\_6500K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 874.6 |
| 2.5°  | 869.8 |
| 5°    | 860.2 |
| 7.5°  | 840.9 |
| 10°   | 816.8 |
| 12.5° | 786.7 |
| 15°   | 749.3 |
| 17.5° | 709.6 |
| 20°   | 665.0 |
| 22.5° | 619.2 |
| 25°   | 572.2 |
| 27.5° | 525.3 |
| 30°   | 478.3 |
| 32.5° | 427.7 |
| 35°   | 375.9 |
| 37.5° | 325.3 |
| 40°   | 277.1 |
| 42.5° | 225.3 |
| 45°   | 173.5 |
| 47.5° | 132.5 |
| 50°   | 96.4  |
| 52.5° | 62.6  |
| 55°   | 44.6  |
| 57.5° | 39.8  |
| 60°   | 36.1  |
| 62.5° | 32.5  |
| 65°   | 28.9  |
| 67.5° | 25.3  |
| 70°   | 21.7  |
| 72.5° | 18.1  |
| 75°   | 14.5  |
| 77.5° | 12.0  |
| 80°   | 9.6   |
| 82.5° | 6.0   |
| 85°   | 3.6   |
| 87.5° | 2.4   |
| 90°   | 0.0   |

(END OF REPORT)